

BC200-CD Conduit to Beam Clamp



CERTIFICATIONS



FEATURES

Eliminates offset bending conduit

Threaded hole on back

Ideal for electrical, mechanical, and HVAC applications

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel


Table 1/2

Catalog Number	Outer Diameter (OD)	EMT Conduit Size	Rigid Conduit Size	Flange Thickness (FT)	Rod Size (RS)	Torque (TQ)
BC200CD0B	0.670" - 0.84"	1/2"	1/2"	1/2" Max	1/4"	3 ft·lbf
BC200CD1B	0.740" - 1.05"	3/4"	3/4"	1/2" Max	1/4"	3 ft·lbf
BC200CD2B	1.000" - 1.31"	1"	1"	1/2" Max	1/4"	3 ft·lbf

Table 2/2

Catalog Number	Static Load (F)	Certifications
BC200CD0B	100lb	cUL, UL
BC200CD1B	100lb	UL, ITB, cUL
BC200CD2B	100lb	cUL, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

