

# **Drop Smooth Rod with Shot-Fire Bracket**



## **CERTIFICATIONS**





## **FEATURES**

Quickly and easily attaches to concrete, steel or composite metal decking

Integrated pin installs easily using powder-actuated or single-shot gas-actuated tools

Works with most standard nVent CADDY spring steel fasteners designed for rod attachments

Rod is rigid and does not require secondary attachment to ceiling grid per NEC 300.11

Stocked inventory - available when you need it

Includes pre-assembled end-cap

Specialized packaging simplifies material handling and minimizes sorting

Rods are ready to install out of the box

## **SPECIFICATIONS**

Finish: Electrogalvanized

Material: Steel

Table 1/1						
Catalog Number	Length (L)	Diameter (Ø)	Α	Static Load (F)		

DR4SF48	48"	0.21"	1.3"	95lbf
DR4SF24	24"	0.21"	1.3"	95lbf
DR4SF36	36"	0.21"	1.3"	95lbf
DR4SF12	12"	0.21"	1.3"	95lbf

# ADDITIONAL PRODUCT DETAILS

Uses Powers Fasteners, Inc. part number 50378.

Static load was established based on a 1-1/8" (28.6 mm) embedment depth and 3,000 psi (20.68 Mpa) normal-weight concrete. For variations in embedment and material please consult www.powers.com.


Pre-assembled drive pin from Powers Fasteners, Inc. works with Powers® C4CZ, Simpson® GCN-MEPKT, SPIT® P1000, P200, P2201, P3500 / PA3500, P35s, P45, P60, P7201, Sniper; Ramset® 721, Cobra, D45 / D60 / D60L, M70, SA270, T3SS, TS750P, TS60P, Viper; Hilti® DX35, DX350 / DX351 / DX36M, DX100 / DX200, DX460, DXA40, DXA41, DXE72 / DX400; Würth® Diva-1, BST-1, BST-2 or equivalent nailers.

For shot-fired supports in seismic design category D, E, or F, maximum load is the lesser of 90 lb (400 N) or the published load.

Exempt from seismic design when supporting conduits less than 2-1/2" (64 mm) trade size, regardless of Ip.

Refer to DeWalt Engineered by Powers Ceiling Clip Assembly ICC-ES Evalution Report ESR-2024 for the allowable load ratings in various substrate material and embedment depths.

# **DIAGRAMS**



## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

# North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

## **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.