

MC/AC Cable to Stud Clip



CERTIFICATIONS



BABA



FEATURES

Manufactured with stabilizer legs for virtually "wobble-free" support

Snap into place on metal stud and beam flange

No tools required for installation

Pre-punched holes in clip allow it to be screwed to wood stud, concrete or block

Compliant with NEC® Article 300.4(d), allowing cable to be positioned a minimum of 1-1/4" from face of stud

Compliant with CEC Rule 12-618 for support of MC/AC cable

Factory riveted assemblies are available for installation on flange, purlin, acoustical tee, drop wire, concrete, block or wood and metal stud

MAC2 snaps in half to accommodate single run of cable effectively making two clips from one

SPECIFICATIONS

Table 1/1

Catalog Number	Material	Finish	Flange Thickness	MC/AC Cable Size
MAC2	Spring Steel	nVent CADDY Armour	1/8" Max	14-2 to 10-3

ADDITIONAL PRODUCT DETAILS

Assemblies allow for support from most main and substructures.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

