

# nVent CADDY Cat HP J-Hook with Strut Attachment Clip



### **CERTIFICATIONS**





## **FEATURES**

Attaches to open side of a strut channel

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

# **SPECIFICATIONS**

**Finish:** Pregalvanized;nVent CADDY Armour

Material: Steel;Spring Steel

Table 1/2						
Catalog Number	Diameter (Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	A

CAT32HPESC	2"	3.97in²	90	60	35	3/8"
CAT16HPESC	1"	1.07in²	20	15	10	3/8"
CAT21HPESC	1 5/16"	2.29in²	50	40	25	3/8"

Table 2/2				
Catalog Number	Static Load (F)			
CAT32HPESC	60lb			
CAT16HPESC	60lb			
CAT21HPESC	60lb			

### ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

# **DIAGRAMS**



### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

