

IceStop Self-Regulating Heating Cable

Data Solutions



nVent RAYCHEM IceStop self-regulating trace heating cables provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

FEATURES

Simple to design

Easy to install: cut to length, meter marks, simple fast RayClic connections

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

GM-2XT for bitumen roofs

SPECIFICATIONS

Min Installation Temperature:	0°F
Nominal Thickness:	0.24in
Nominal Width:	0.54in
Nominal Cable Weight:	92lb/ft
Color:	Black
Ground Path Type:	Braid
Conductor Material:	Nickel-Plated Copper

Table 1/2

Catalog Number	Article Number	Supply Voltage	Nominal Power Output, In Air @ 32°F, 120V	Nominal Power Output, In Air @ 32°F, 240V	Nominal Power Output, In Ice Water @ 32°F, 120V	Nominal Power Output, In Ice Water @ 32°F, 240V

092961-000	GM-2XT	208 – 240V		6W/ft		12W/ft
446105-000	GM-2X	208 – 240V		6W/ft		12W/ft
832100-000	GM-1X	120V	6W/ft		12W/ft	
900069-000	GM-1XT	120V	6W/ft		12W/ft	

Table 2/2

Catalog Number	Article Number	Outer Jacket Material
092961-000	GM-2XT	Fluoropolymer
446105-000	GM-2X	Modified Polyolefin
832100-000	GM-1X	Modified Polyolefin
900069-000	GM-1XT	Fluoropolymer

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE