

Enlogic Basic PDU

Data Solutions



The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

FEATURES

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

SPECIFICATIONS

Table 1/6

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EB0316	Enlogic	Basic PDU	Socket Strip	(16) 5-20R	16	Black
EB0323	Enlogic	Basic PDU	Socket Strip	(22) 5-20R	22	Black
EB0336	Enlogic	Basic PDU	Socket Strip	(36) C13, (6) C19	42	Black
EB0803	Enlogic	Basic PDU	Socket Strip	(24) C13, (3) C19, (3) 5-20R	30	Black
EB0805-S	Enlogic	Basic PDU	Socket Strip	(36) C13, (6) C19	42	Black
EB0815	Enlogic	Basic PDU	Socket Strip	(24) C13, (12) C19	36	Black
EB0851	Enlogic	Basic PDU	Socket Strip	(21) C13/C15, (21) C13/C15/C19/C21	42	Black

CatalogNumber	Product Family	Type	Product Type	Socket Type	SocketQuantity	Color
EB0860	Enlogic	Basic PDU	Socket Strip	(24) C13/C15, (24) C13/C15/C19/C 21	48	Black
EB0902	Enlogic	Basic PDU	Socket Strip	(12) C13, (12) C19	24	Black
EB0952	Enlogic	Basic PDU	Socket Strip	(21) C13/C15, (21) C13/C15/C19/C 21	42	Black
EB09JA	Enlogic	Basic PDU	Socket Strip	(18) C13/C15, (18) C13/C15/C19/C 21	36	Black
EB0360	Enlogic	Basic PDU	Socket Strip	(16) C13/C15	20	Black

Table 2/6						
Catalog Number	Cable Length	Switched Outlets	Circuit Breaker	Power Rating	Circuit Breaker Quantity	Interrupt Rating
EB0316	10ft	No	No Circuit BreakerA	1.9 kVA	0	
EB0323	10ft	No	20 A, 1-pole, Hy-MagA	2.9 kVA	2	5kAIC
EB0336	10ft	No	20 A, 2-pole, Hy-MagA	5.0 kVA	2	5kAIC
EB0803	10ft	No	20 A, 2-pole, Hy-MagA	8.6 kVA	3	5kAIC
EB0805-S	10ft	No	20 A, 2-pole, Hy-MagA	8.6 kVA	3	5kAIC
EB0815	10ft	No	20 A, 1-pole, Hy-MagA	17.3 kVA	6	
EB0851	6ft	No	20 A, 2-pole, Hy-MagA	8.6 kVA	3	5kAIC
EB0860	10ft	No	20 A, 1-pole, Hy-MagA	17.3 kVA North America, 22.1 kVA International	6	
EB0902	10ft	No	20 A, 2-pole, Hy-MagA	17.3 kVA	6	5kAIC

CatalogNumber	Cable Length	Switched Outlets	Circuit Breaker	Power Rating	Circuit Breaker Quantity	InterruptRating
EB0952	6ft	No	20 A, 2-pole, Hy-MagA	17.3 kVA	6	5kAIC
EB09JA	6ft	No	20 A, 1-pole, Hy-MagA	34.6 kVA North America, 43.5 kVA International	12	
EB0360	10ft	No	16 A, 1-pole, Hy-Mag	7.4 kVA	2	5kAIC

Table 3/6

Catalog Number	Input Voltage	Phase	Nominal Power Output	Nominal Voltage	Number of Output Voltages	Number of Phases
EB0316	120V	1 PH	120VAC	120V	16	1
EB0323	120V	1 PH	120VAC	120V	22	1
EB0336	208V	1 PH	208VAC	208V	42	1
EB0803	208V	3 PH WYE	120VAC	208V	30	3
EB0805-S	208V	3 PH Delta	208VAC	208V	42	3
EB0815			208VAC	415V	36	
EB0851			120VAC	208V	42	3
EB0860			208VAC	415V		
EB0902	208V	3 PH Delta	208VAC	208V	24	3
EB0952	208V	3 PH Delta	208VAC	208V	42	3
EB09JA			208VAC	415V	36	
EB0360			230VAC	230V	20	1

Table 4/6

Catalog Number	On/Off Switch Included	Amperage (Derated Amperage)	Output Voltage	Rack Units	Plug Type	Metering Type
EB0316	No	20 A (16 A)	120VAC	0U	NEMA L5-20P	None
EB0323	No	30A (24A)	120VAC	0U	NEMA L5-30P	None
EB0336	No	30A (24A)	208VAC	0U	NEMA L6-30P	None
EB0803	No	30A (24A)	120 – 208VAC	0U	NEMA L21-30P	None
EB0805-S	No	30A (24A)	208VAC	0U	NEMA L15-30P	None
EB0815	No	30A (24A)	208VAC	0U	IEC 60309 530P6 (IP44)	None
EB0851	No	30A (24A)	120 – 208VAC	0U	NEMA L21-30P	None
EB0860	No	30 A (24 A) North America, 32 A International	208 – 230VAC	0U	IEC 60309 530P6/532P6	None
EB0902	No	60 A (48 A)	208VAC	0U	IEC 60309 460P9 (IP44)	None
EB0952	No	60 A (48 A)	208VAC	0U	IEC 60309 460P9 (IP44)	None
EB09JA	No	60 A (48 A) North America, 63 A International	208 – 230VAC	0U	IEC 60309 560P6/563P6	None
EB0360	No	32 A	230VAC	0U	IEC 60309 332P6 (IP44)	None

Table 5/6

Catalog Number	Removable Input Cable	Material	Finish	Height	Width	Depth
EB0316	Yes	Steel	Powder Coated	32.17in	2.05in	2.09in
EB0323	No	Steel	Powder Coated	32.17in	2.05in	2.09in

CatalogNumber	Removable Input Cable	Material	Finish	Height	Width	Depth
EB0336	No	Steel	Powder Coated	58.66in	2.05in	2.09in
EB0803	No	Steel	Powder Coated	58.66in	2.05in	2.09in
EB0805-S	No	Steel	Powder Coated	68.9in	2.05in	2.09in
EB0815	No	Steel	Powder Coated	68.9in	2.05in	2.09in
EB0851	No	Steel	Powder Coated	70.8in	2.2in	2.17in
EB0860	No	Steel	Powder Coated	58.66in	2.2in	2.17in
EB0902	No	Steel	Powder Coated	68.9in	2.05in	2.09in
EB0952	No	Steel	Powder Coated	70.8in	2.2in	2.95in
EB09JA	No	Steel	Powder Coated	37.99in	4.48in	2.95in
EB0360	No	Steel	Powder Coated	32.12in	2.05in	2.09in

Table 6/6

Catalog Number	Weight	Package Quantity
EB0316	7.92lb	1
EB0323	7.92lb	1
EB0336		1
EB0803	17.2lb	1
EB0805-S		1
EB0815		1
EB0851	18.7lb	1

Catalog Number	Weight	Package Quantity
EB0860		1
EB0902		1
EB0952	28.6lb	1
EB09JA		1
EB0360	7.92lb	1

ADDITIONAL PRODUCT DETAILS

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE