

# Air Terminal Base, Horizontal Bond, Imperial Thread



### **CERTIFICATIONS**





## **FEATURES**

Bonds directly to horizontal structural steel surface


#### **SPECIFICATIONS**


Table 1/2							
Catalog Number	Material	Thread Size (TS)	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Depth (D)	Height (H)	
LPA34058	Aluminum	5/8" UNC	0.2"	1/4"	2"	0.95"	
LPA34012	Aluminum	1/2" UNC	0.2"	1/4"	2"	0.95"	
LPC34058	Copper	5/8" UNC	0.2"	1/4"	2"	0.95"	
LPC34012	Copper	1/2" UNC	0.2"	1/4"	2"	0.95"	

CatalogNumber	Material	Thread Size (TS)	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Depth (D)	Height (H)
LPC34038	Copper	3/8" UNC	0.2"	1/4"	2"	0.95"

Table 2/2							
Catalog Number	Width (W)	Unit Weight	Certifications				
LPA34058	4"	0.16 lb	E202878-Combined_CoC, E202878-Combined_CoC				
LPA34012	4"	0.16 lb	E202878-Combined_CoC, E202878-Combined_CoC				
LPC34058	4"	0.53 lb					
LPC34012	4"	0.53 lb					
LPC34038	4"	0.53 lb					

## **DIAGRAMS**





## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

 $^{\triangle}$  WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE