

Special Track Work Mold Only, Power

Data Solutions



FEATURES

Replacement molds designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

SPECIFICATIONS

Rail Type:	Crane Rail Profiles
Material:	Graphite
Bond Terminal Style:	J

Table 1/1

Catalog Number	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBJT503LHM	2/0 Concentric	0.42in	T5	Left Hand
PBJT503RHM	2/0 Concentric	0.42in	T5	Right Hand
PBJT52QLHM	4/0 Concentric	0.53in	T5	Left Hand
PBJT52QM	4/0 Concentric	0.53in	T5	Left and Right Hand

Catalog Number	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBJT52QRHM	4/0 Concentric	0.53in	T5	Right Hand
PBJT52WLHM	250 kcmil Ropelay	0.75in	T5	Left Hand
PBJT52WM	250 kcmil Ropelay	0.75in	T5	Left and Right Hand
PBJT52WRHM	250 kcmil Ropelay	0.75in	T5	Right Hand

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE