

Modular TDX Panel Protector, 400 kA



CERTIFICATIONS



FEATURES

Transient Discriminating (TD) Technology provides increased service life

Modular design allows easy replacement of surge modules

Built-in features include TD Technology, thermal protection, short circuit current cartridge fusing and a surge counter

Status indication flag per mode, voltage presence LEDs, audible alarm and voltage-free contacts providing remote status monitoring

400kA 8/20 μ s maximum surge rating provides protection suitable for service entrance, main-distribution panels and highly exposed applications


SPECIFICATIONS

Catalog Number	TDX400S120/240	TDX400S120/208	TDX400S277/480
Nominal System Voltage (Un)	120/240 V	120/208 V	277/480 V
Distribution System	1Ph 3W+G	3Ph 4W+G	3Ph 4W+G
Max Continuous Operating Voltage (Uc)	170/276 VAC	170/276 VAC	320/550 VAC
Stand-off Voltage	240/480 VAC	240/415 VAC	480/831 VAC

Catalog Number	TDX400S120/240	TDX400S120/208	TDX400S277/480
Frequency	50 - 60 Hz	50 - 60 Hz	50 - 60 Hz
Short Circuit Current Rating (SCCR)	200kA	200kA	200kA
Nominal Discharge Current (In), IEC	40kA 8/20 μ s	40kA 8/20 μ s	40kA 8/20 μ s
Nominal Discharge Current (In), UL	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s
Max Discharge Current (Imax), Per Phase	400kA 8/20 μ s	400kA 8/20 μ s	400kA 8/20 μ s
Impulse Current (Iimp), Per Mode	25kA 10/350 μ s	25kA 10/350 μ s	25kA 10/350 μ s
Voltage Protection Rating (VPR), L-N	800 V @ 3 kA	800 V @ 3 kA	1200 V @ 3 kA
Protection Modes	L-N L-PE N-PE	L-N L-PE N-PE	L-N L-PE N-PE
Status Indication	LED Mechanical flag Audible alarm	LED Mechanical flag Audible alarm	LED Mechanical flag Audible alarm
Surge Counter	Yes	Yes	Yes
Technology	TD technology with thermal disconnect Over-current replaceable cartridge fusing	TD technology with thermal disconnect Over-current replaceable cartridge fusing	TD technology with thermal disconnect Over-current replaceable cartridge fusing
Remote Contacts	Yes	Yes	Yes
Lead Length	30"	30"	30"
Lead Size imperial	#10	#10	#10
Ground Lead Length	36"	36"	36"
Temperature	-40 to 176 °F	-40 to 176 °F	-40 to 176 °F
Enclosure Material	Metal	Metal	Metal
Enclosure Rating	IP 20 NEMA®-12/3R	IP 20 NEMA®-12/3R	IP 20 NEMA®-12/3R
Mounting	3/4" straight nipple	3/4" straight nipple	3/4" straight nipple
Depth (D)	3 1/4"	3 1/4"	3 1/4"
Height (H)	10.4"	10.4"	10.4"
Width (W)	10.32"	10.32"	10.32"
Unit Weight	14 lb	14 lb	14 lb
Certification Details	UL® 1449 Edition 5 Type 1/2, 20 kA Mode	UL® 1449 Edition 5 Type 1/2, 20 kA Mode	UL® 1449 Edition 5 Type 1/2, 20 kA Mode

Catalog Number	TDX400S120/240	TDX400S120/208	TDX400S277/480
Complies With	ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 μ s, 10 kA 10/350 μ s IEC® 61643-1 Class I, Class II	ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 μ s, 10 kA 10/350 μ s IEC® 61643-1 Class I, Class II	ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 μ s, 10 kA 10/350 μ s IEC® 61643-1 Class I, Class II
Replacement Module	TDS150M150	TDS150M150	TDS150M277

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE