

Replacement Module for UTB, Dual Pair



CERTIFICATIONS



FEATURES

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions


Surge rating to 20 kA 8/20 μ s is ideal for exposed wiring

SPECIFICATIONS

Catalog Number	UTB110DPM	UTB15DPM	UTB30DPM	UTB5DPM	UTB60DPM
Nominal System Voltage (Un)	100 - 120 VAC 60 - 154 VDC	3 - 10 VAC 5 - 15 VDC	10 - 21 VAC 15 - 30 VDC	0 - 3 VAC 0 - 5 VDC	21 - 42 VAC 30 - 60 VDC
Max Continuous Operating Voltage (Uc)	150 VAC 170 VDC	12 VAC 18 VDC	23 VAC 33 VDC	5 VAC 7 VDC	45 VAC 64 VDC
Rated Load Current (IL)	800mA	800mA	800mA	800mA	800mA
Frequency	3 MHz	1 MHz	2 MHz	0.5 MHz	3 MHz
Loop Resistance	0.6 Ω	0.6 Ω	0.6 Ω	0.6 Ω	0.6 Ω

Catalog Number	UTB110DPM	UTB15DPM	UTB30DPM	UTB5DPM	UTB60DPM
Max Discharge Current (Imax), L+L-PE	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s
Protection Modes	Common Differential	Common Differential	Common Differential	Common Differential	Common Differential
Technology	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)
Voltage Protection Level (Up), L-L	220 V @ 3 kA	25 V @ 3 kA	44 V @ 3 kA	10 V @ 3 kA	85 V @ 3 kA
Temperature	-4 to 149 °F	-4 to 149 °F	-4 to 149 °F	-4 to 149 °F	-4 to 149 °F
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Depth (D)	1.7"	1.7"	1.7"	1.7"	1.7"
Height (H)	2.57"	2.57"	2.57"	2.57"	2.57"
Width (W)	0.47"	0.47"	0.47"	0.47"	0.47"
Unit Weight	0.05 lb	0.05 lb	0.05 lb	0.05 lb	0.05 lb
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE