

EDT2 Enhanced DIN Rail Surge Protection Class II, 1+0 Mode, 240 V Un

CATALOG NUMBER

EDT230010R



CERTIFICATIONS



FEATURES

Includes nVent ERICO TD Technology to ensure reliability throughout adverse voltage conditions

Enhanced temporary over voltage (TOV) withstand capability

External back-up fuse is not required up to 315 A (IEC only)

Compact, yet high surge rated pluggable design, using minimum DIN rail width.

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring

PRODUCT ATTRIBUTES

Nominal System Voltage (U_n): 240 V

Max Continuous Operating Voltage (U_c): 300 V

Nominal Discharge Current (In), IEC: 20kA 8/20 μ s

Max Discharge Current (Imax), IEC: 50kA 8/20 μ s

Voltage Protection Level (Up): 1650V

Back-Up Fuse @ Isccr: 250 A @ 50 kA;315 A @ 25 kA

Frequency: 50 - 60 Hz

Response Time: 25 ns Max

Protection Modes: L-PE;N-PE;L-PEN;L-N

Short Circuit Current Rating (Isccr): 25kA;50kA

Temporary Over Voltage 120 min (Ut/mode): 442 V Withstand

Nominal Discharge Current (In), UL: 20kA 8/20 μ s

Short Circuit Current Rating (SCCR): 150kA

Voltage Protection Rating (VPR): 1200V

Technology: Thermal Disconnect

Connection, Solid: 35 mm² Max

Connection, Solid: #2 max

Connection, Stranded: #4 max

Torque (TQ): 3.32 ft·lbf

Humidity: 5 - 95

Temperature: -31 to 185 °F

Enclosure Material: UL® 94V-0 Thermoplastic

Enclosure Rating: IP 20

Mounting: 35 mm top hat DIN rail

Remote Contact Switching Capacity: 1 A @ 250 VAC;1 A @ 125 VAC;0.5 A @ 48 VDC;0.5 A @ 24 VDC;0.5 A @ 12 VDC

Remote Contacts: Yes

Status Indication: Mechanical flag

Depth (D): 2.72"

Height (H): 3.54"

Width (W): 0.71"


Unit Weight: 0.31 lb

Certification Details: UL® 1449 Edition 5 Type 1CA

Complies With: EN 61643-11 Type 2;IEC® 61643-11 Class II

Replacement Module: EDT2300M

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE