

Modular TDX Panel Protector, 200 kA with Surge Counter



CERTIFICATIONS



FEATURES

Transient Discriminating (TD) Technology provides increased service life

Modular design allows easy replacement of surge modules

Built-in features include TD Technology, thermal protection and short circuit current fusing

Compact NEMA®-4 enclosure design can be flush mounted or installed in a small space

Status indication flag per mode, voltage presence LEDs, audible alarm and voltage-free contacts providing remote status monitoring

200kA 8/20µs maximum surge rating provides protection suitable for service entrance, main-distribution panels and highly exposed applications


SPECIFICATIONS

Catalog Number	TDX200S120240D	TDX200S347600
Service Configuration	Delta	
Nominal System Voltage (Un)	120/240 V	347/600 V

Catalog Number	TDX200S120240D	TDX200S347600
Distribution System	3PhΔ 4W+G	3Ph 4W+G
Max Continuous Operating Voltage (Uc)	170/276 VAC	550/1100 VAC
Stand-off Voltage	240/415 VAC	790/1370 VAC
Frequency	50 - 60 Hz	50 - 60 Hz
Short Circuit Current Rating (SCCR)	200kA	200kA
Nominal Discharge Current (In), IEC	40kA 8/20 μs	40kA 8/20 μs
Nominal Discharge Current (In), UL	20kA 8/20 μs	20kA 8/20 μs
Max Discharge Current (Imax), Per Phase	200kA 8/20 μs	200kA 8/20 μs
Impulse Current (Iimp), Per Mode	25kA 10/350 μs	25kA 10/350 μs
Voltage Protection Rating (VPR), L-N	600 V @ 3 kA 1200 V @ 20 kA	1800 V @ 3 kA 2600 V @ 20 kA
Protection Modes	L-N L-PE N-PE	L-N L-PE N-PE
Status Indication	LED Mechanical flag Audible alarm	LED Mechanical flag Audible alarm
Technology	TD technology with thermal disconnect Over-current replaceable cartridge fusing EMI/RFI filter	TD technology with thermal disconnect Over-current replaceable cartridge fusing EMI/RFI filter
Remote Contacts	Yes	Yes
Lead Length	30"	30"
Lead Size imperial	#10	#10
Ground Lead Length	36"	36"
Temperature	-40 to 176 °F	-40 to 176 °F
Enclosure Material	Metal	Metal
Enclosure Rating	IP 65 NEMA®-4	IP 65 NEMA®-4
Mounting	3/4" straight nipple	3/4" straight nipple
Surge Counter	Yes	Yes
Depth (D)	3.07"	3.07"
Height (H)	9.45"	9.45"
Width (W)	5.12"	5.12"
Unit Weight	4.4 lb	4.4 lb
Certification Details	UL® 1449 Edition 5 Type 2, 20 kA Mode	UL® 1449 Edition 5 Type 2, 20 kA Mode

Catalog Number	TDX200S120240D	TDX200S347600
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 µs, 10 kA 10/350 µs IEC® 61643-1 Class I, Class II	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 µs, 10 kA 10/350 µs IEC® 61643-1 Class I, Class II
Replacement Module	TDS150M150 TDS150M240	TDS150M560

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE