

Universal Transient Barrier, Dual Pair



CERTIFICATIONS



FEATURES

Compact design universal transient barrier provides protection of low-voltage circuits and transducers

Separate plug and base design allows hot swappable module replacement

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions

Surge rating to 20 kA 8/20 μ s is ideal for exposed wiring

Allows for protection of 25 analog signals or 50 digital signals per linear foot (0,3 m) of DIN rail space

SPECIFICATIONS

Catalog Number	UTB110DP	UTB15DP	UTB30DP	UTB5DP	UTB60DP
Nominal System Voltage (Un)	100 - 120 VAC 60 - 154 VDC	3 - 10 VAC 5 - 15 VDC	10 - 21 VAC 15 - 30 VDC	0 - 3 VAC 0 - 5 VDC	21 - 42 VAC 30 - 60 VDC
Max Continuous Operating Voltage (Uc)	150 VAC 170 VDC	12 VAC 18 VDC	23 VAC 33 VDC	5 VAC 7 VDC	45 VAC 64 VDC

Catalog Number	UTB110DP	UTB15DP	UTB30DP	UTB5DP	UTB60DP
Rated Load Current (IL)	800mA	800mA	800mA	800mA	800mA
Frequency	3 MHz	1 MHz	2 MHz	0.5 MHz	3 MHz
Loop Resistance	0.6 Ω	0.6 Ω	0.6 Ω	0.6 Ω	0.6 Ω
Max Discharge Current (Imax), L+L-PE	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs
Protection Modes	Common Differential	Common Differential	Common Differential	Common Differential	Common Differential
Technology	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)
Voltage Protection Level (Up), L-L	220 V @ 3 kA	25 V @ 3 kA	44 V @ 3 kA	10 V @ 3 kA	85 V @ 3 kA
Connection, Stranded	#18 min	#18 min	#18 min	#18 min	#18 min
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail	35 mm top hat DIN rail	35 mm top hat DIN rail	35 mm top hat DIN rail
Temperature	-4 to 149 °F	-4 to 149 °F	-4 to 149 °F	-4 to 149 °F	-4 to 149 °F
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20 NEMA®-1	IP 20 NEMA®-1	IP 20 NEMA®-1	IP 20 NEMA®-1	IP 20 NEMA®-1
Depth (D)	3.35"	3.35"	3.35"	3.35"	3.35"
Height (H)	3.54"	3.54"	3.54"	3.54"	3.54"
Width (W)	0.47"	0.47"	0.47"	0.47"	0.47"
Unit Weight	0.2 lb	0.2 lb	0.2 lb	0.2 lb	0.2 lb
Certification Details	UL® 497B	UL® 497B	UL® 497B	UL® 497B	UL® 497B
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C
Replacement Module	UTB110DPM	UTB15DPM	UTB30DPM	UTB5DPM	UTB60DPM

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE