

Telecom Main Grounding Busbar



CERTIFICATIONS



FEATURES

Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

SPECIFICATIONS

Thickness (T): 1/4"
Width (W): 4"
Material: Copper

Table 1/3

Catalog Number	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 (HS1)	Hole Size 1 Number of Pairs
TMGBA12L15PT	Yes	12"	9"	5/16"	15
TMGBA12L15P	No	12"	9"	5/16"	15

Catalog Number	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 (HS1)	Hole Size 1 Number of Pairs
TMGBA24L33PT	Yes	24"	18"	5/16"	33
TMGBA20L27P	No	20"	9"	5/16"	27
TMGBA29L41PT	Yes	29"	18"	5/16"	41


Table 2/3

Catalog Number	Hole Size 2 (HS2)	Hole Size 2 Number of Pairs	A	B	C
TMGBA12L15PT	7/16"	3	1"	1 1/8"	5/8"
TMGBA12L15P	7/16"	3	1"	1 1/8"	5/8"
TMGBA24L33PT	7/16"	5	1"	1 1/8"	5/8"
TMGBA20L27P	7/16"	3	1"	1 1/8"	5/8"
TMGBA29L41PT	7/16"	5	1"	1 1/8"	5/8"

Table 3/3

Catalog Number	D
TMGBA12L15PT	5/8"
TMGBA12L15P	5/8"
TMGBA24L33PT	5/8"
TMGBA20L27P	5/8"
TMGBA29L41PT	5/8"

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE