

TSF Replacement Module



CERTIFICATIONS



FEATURES


Replacement module for Transient Surge Filter

SPECIFICATIONS

Catalog Number	TSF24MDSD	TSF120MTDS	TSF240MTDS
Nominal System Voltage (Un)	24 VAC	120 - 150 VAC	220 - 240 VAC
Max Continuous Operating Voltage (Uc)	30 VAC/38 VDC	170 VAC	275 VAC
Nominal Discharge Current (In)	3kA 8/20 μs	3kA 8/20 μs	3kA 8/20 μs
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Temperature	-40 to 176 °F	-40 to 176 °F	-40 to 176 °F
Module Width	1 M	1 M	1 M
Depth (D)	1.92"	1.92"	1.92"
Height (H)	1.78"	1.78"	1.78"
Width (W)	0.71"	0.71"	0.71"

Catalog Number	TSF24MDSD	TSF120MTDS	TSF240MTDS
Unit Weight	0.15 lb	0.15 lb	0.15 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 **APAC**

Shanghai: + 86 21 2412

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN

ILSCO SCHROFF

TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.