

Concept HMI Enclosure Black Handle Type 4, 370x400x120mm, Light Gray, Mild Steel

CATALOG NUMBER

CP374012



A traditional landscape-oriented HMI enclosure with handles made of light-gray steel, the Concept HMI Enclosure is unique among HMI enclosure systems when you need a range of customization options. This pendant- or pedestal-mounted system has many possible configurations and modifications, including a removable front plate that makes it easy to install HMI components, an optional door panel can be mounted in the hinged rear door and the ability to accommodate cutouts anywhere on the enclosure.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File Number E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. E61997

NEMA Type 4, 12

IEC 60529, IP66

FEATURES

Pre-drilled hole in top for pendant arm mounting

Pedestal mounting when enclosure is inverted

Integral aluminum handle extrusions have a comfort grip that extends the length of the profile; available in black or blue

Hinged rear corner-formed door has a single-point latch, seamless foam-in-place gasket and panel studs

Aluminum removable front plate is .125-in aluminum

Grounding stud on body; bonding provision on door

Simple easy-to-remove and install hinge pins with built-in captive clip

High-torque threadless studs and fasteners on door for mounting optional door panel

PRODUCT ATTRIBUTES

Article Number: 14726

Height (H): 14.57in

Width (W): 15.75in

Weight: 24.7lb

Technical drawing of the 87791732 window frame. The drawing includes three views: a front view, a side view, and a detail view of the corner. Dimensions are provided in millimeters (mm) and inches (in). The front view shows a rectangular frame with dimensions A (height), B (width), C (top flange), D (left flange), E (bottom flange), and M (inner width). The side view shows the frame's profile with dimensions N (inner depth), O (outer depth), and P (flange thickness). The detail view shows a circular cross-section of the corner with dimensions Q (outer radius), R (inner radius), and S (flange thickness). The part number 87791732 is indicated at the bottom.

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE