

EuropacPRO 19" Subrack Kit for Railway, Retrofit Shielding, EN 50155

Power Utilities



Subrack for Railway applications, conform to EN50155 standard, non-shielded.

CERTIFICATIONS



FEATURES

Shock and vibration tested to EN 50155, part 12.2.11

The 19" bracket is firmly fixed to the side panel (toxic-welded) and is especially suited for high mechanical stresses (vibration resistance)

Modifications such as cutouts, different finishes or dimensions available

IP 20, in accordance with IEC 60529

The double 19" screwing position adds to additionally safety (NFF standard)

Supplied as space-saving flat-pack

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Package Quantity	For Mounting	Gasket Type	Shock and Vibration Tolerance	Handle Included
----------------	-------------	------------------	--------------	-------------	-------------------------------	-----------------

21500-078	6 U	1	Backplane	Textile	5 g (force)	Yes
21500-077	3 U	1	Backplane	Textile	5 g (force)	Yes

Table 2/2

Catalog Number	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
21500-078	Rack	IEC 60297-3-103, EN 50155 part 12.2.11	No	Subrack/Chassis	84 HP
21500-077	Rack	IEC 60297-3-103, EN 50155 part 12.2.11	No	Subrack/Chassis	84 HP

ADDITIONAL PRODUCT DETAILS

Test reports are available online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE