

# ElectroMelt Self-Regulating Heating Cable



nVent RAYCHEM ElectroMelt EM2-XR is a rugged and robust self-regulating heating cable used to prevent snow and ice formation on ramps, loading bays, external stairs and access ways. Power output is 90 W/m at 0 °C.

## FEATURES

Simple to design

Robust and easy to install: cable is resistant to damage during installation, cut to length

Safe and efficient in operation: no overheating, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

## SPECIFICATIONS

Table 1/2

Catalog Number	Item Name	Supply Voltage	Nominal Power Output @ 32°F, 240V	Outer Jacket Material	Max Circuit Length	Color
449561-000	EM2-XR	208 – 277 V	32 W/ft	Modified Polyolefin	278 ft	Orange

Table 2/2

Catalog Number	Item Name	Nominal Width	Nominal Thickness	Ground Path Type	Min Installation Temperature
449561-000	EM2-XR	0.74 in	0.37 in	Braid	0 °F

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,  
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM   PYROTENAX   TRACER   NUHEAT**