

nVent LENTON Connect S2 Series Shear Bolt Coupler, Epoxy



Coated reinforcing bar is used in place of plain reinforcing bars to protect against corrosion. Typical applications include bridges, parking structures, pavement, marine structures and repair work. nVent LENTON couplers and mechanical anchors are available in multiple coatings to meet specific job requirements.

FEATURES

Requires no special bar end preparation such as sawing

Installs quickly and easily using simple, off-the-shelf hand tools

Bolt heads shear off when bolt torque is achieved, providing for simple visual inspection

Designed to work as a one-step transition/reducer

Rebar centering pin can be removed to allow the coupler to fully pass onto the reinforcing bar for applications such as closure pours

Complies to ACI 318 Type 1 performance on ASTM A706 and ASTM A615 grade 60 reinforcing bar

SPECIFICATIONS

Finish Standard:	ASTM® A775/A775M and AASHTO M284
Finish:	Epoxy Coated
Material:	Steel
100% U.S. Domestic Content:	Yes

Table 1/2

Catalog Number	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Length 1 (L1)	Length 2 (L2)	Socket Width (SW)
LC16S2ESD	#4, #5	10M, 15M	1.63"	3 1/2"	1.7"	1/2"
LC20S2ESD	#6	20M	1.9"	5.1"	2 1/2"	1/2"

CatalogNumber	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Length 1 (L1)	Length 2 (L2)	Socket Width (SW)
LC22S2ESD	#7		2"	6.9"	3.4"	1/2"
LC25S2ESD	#8	25M	2.38"	8.7"	4.3"	5/8"
LC28S2ESD	#9	30M	2.8"	8.7"	4.3"	3/4"
LC32S2ESD	#10		3"	11.2"	5.4"	3/4"
LC36S2ESD	#11	35M	3.13"	13.7"	6.7"	3/4"

Table 2/2

Catalog Number	Number of Bolts	Torque (TQ)	Unit Weight
LC16S2ESD	4	85 ft·lbf	1.5 lb
LC20S2ESD	6	85 ft·lbf	2.7 lb
LC22S2ESD	8	85 ft·lbf	3.9 lb
LC25S2ESD	8	193 ft·lbf	7.6 lb
LC28S2ESD	6	597 ft·lbf	10.8 lb
LC32S2ESD	8	597 ft·lbf	15.2 lb
LC36S2ESD	10	597 ft·lbf	19.6 lb

Designed to Meet: AASHTO;ACI 318 Type 1 (125% Specified Yield);CAN/CSA - N287.2/.3/.4;IBC Type 1 (125% Specified Yield);US Army Corps of Engineers;CAN/CSA - A23.3


ADDITIONAL PRODUCT DETAILS

Bolt length may vary after the bolt heads are sheared off. Bolt heads are not required to be removed as long as the appropriate bolt torque is achieved.

Refer to complete installation instructions provided with the product or available at nVent.com/LENTON prior to commencing installation.

See instructions for installation equipment recommendations.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE