

# P9J Weldable Position Coupler for Nuclear Applications



The nVent LENTON P9J Weldable Position Coupler for Nuclear Applications is designed for quick and easy connections of reinforcing steel bar to structural steel sections and plates. The nuclear construction industry demands scrutiny throughout the entire product life-cycle and nVent LENTON is here to be your technical expert. All weldable couplers are assigned unique part numbers to ensure detailed product documentation—including full product traceability—is performed to individual customer requirements.

When it comes to nuclear construction, precision, reliability, and compliance are non-negotiable. That's why leading contractors and engineers around the world turn to nVent LENTON—a global leader in mechanical rebar splicing systems engineered for the most demanding environments.

## FEATURES

Designed for connecting reinforcing bar perpendicular to structural steel sections or plates when the mating bar cannot be rotated and is free to move in its axial direction

Ideal for connecting hooked reinforcing bar to structural steel elements

Internally taper threaded on one end, with the other end prepared for welding

Machined from weldable grades of steel

Digital model available in nVent BIM Library

## SPECIFICATIONS

<b>Finish:</b>	Plain
<b>Material:</b>	Steel
<b>100% U.S. Domestic Content:</b>	Yes

Table 1/2

Catalog Number	Rebar Size, US	Rebar Size, Canada	Diameter 1 (Ø1)	Diameter 2 (Ø2)	Length 1 (L1)	Length 2 (L2)
EL20P9JQ	#6	20M	2"	1.63"	4.15"	4.47"

CatalogNumber	Rebar Size, US	Rebar Size, Canada	Diameter 1(Ø1)	Diameter 2(Ø2)	Length 1 (L1)	Length 2 (L2)
EL22P9JQ	#7		2"	1 1/2"	4.34"	4.65"
EL25P9JQ	#8	25M	2"	1.38"	4.53"	4.84"
EL28P9JQ	#9	30M	3"	2 1/2"	4.47"	4.78"
EL32P9JQ	#10		3"	2.38"	4.72"	5.03"
EL36P9JQ	#11	35M	3"	2 1/4"	4.97"	5.28"

Table 2/2


Catalog Number	Bar Depth (BD)	Coupler Body (CB)	Unit Weight
EL20P9JQ	1.09"	2.56"	2.6 lb
EL22P9JQ	1.26"	2 3/4"	2.7 lb
EL25P9JQ	1.36"	2.94"	2.7 lb
EL28P9JQ	1.49"	2.88"	6 lb
EL32P9JQ	1.58"	3.13"	6.1 lb
EL36P9JQ	1.68"	3.38"	6.4 lb

**Designed to Meet:** AASHTO;ABNT NBR 8548:1984;ACI 318 Type 1 (125% Specified Yield);ACI 318 Type 2 (Specified Tensile);ACI 349;ACI 359;AS3600

## ADDITIONAL PRODUCT DETAILS

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE