

PD Pro Series



nVent RAYCHEM PD Pro is an energy efficient control unit for medium-sized snow melting and gutter de-icing applications that do not require a control panel. Operating at 100-277 VAC, it can be used to control a single heat tracing circuit or switch multiple circuits through a contactor. It interfaces with up to two sensors. Also available with integral 30 mA ground fault protection.

FEATURES

- Simple and fast to install and operate
- Energy saving, with capability for 2 snow sensors (GIT-1, CIT-1 or SIT-6E sensors, any combination)
- Automatic and manual override control, 'heater cycle control button' allows manual initiation or cancellation
- Adjustable hold-on timer continues heater operation for up to 8 hours after snow stops, to ensure complete melting
- Optional RCU-3 remote control unit, for convenient monitoring and control
- Reliable during long life: 2 year product warranty available, maintenance free

SPECIFICATIONS

Depth:	4 in
IP Rating:	4X
Height:	5.5 in
Width:	8.125 in
Current Rating:	30 A
Supply Voltage:	100 – 277 V
Material:	Polycarbonate

Catalog Number	Item Name
P000001508	PD-PRO
P000001509	GF-PRO

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT