

VMEbus J2 Backplane 3 U, 4 Slots

CATALOG NUMBER

23001-034



The nVent SCHROFF VMEbus Backplanes have outstanding high-frequency noise suppression and very high MTBF values due to ceramic capacitors and SMD fabrication technology.

CERTIFICATIONS



FEATURES

In accordance with ANSI/VITA 1-1994 VME64 standard

3 U with J2 plane

Connection or isolation between the digital GND and chassis GND can be changed via screw

Termination passive

Supply voltages can be provided via powerbugs (ring tag M4) or FASTONs

Multiple backplanes can be placed side by side without loss of slot space

PRODUCT ATTRIBUTES

Product Type: Backplane

Number of Slots: 4

Rack Height: 3U

Backplane Type: VMEbus, J2

System Slot: Slot 1 Left

Slot Width: 4HP

Connector Type: DIN 41612, C96

Power Connector Type: Power Bugs for M4 Cable Lugs

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Other configurations available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE