


MultipacPRO Mounting Plate



Mounting plates are designed for the mounting of heavy components, e.g. transformers.

CERTIFICATIONS



FEATURES

Mounting plates are designed for the mounting of heavy components, e.g. transformers

Bolted laterally inside on a 19" chassis

SPECIFICATIONS

Material:	Aluminum
Works With:	Chassis
Product Type:	Mounting Plate
Product Family:	MultipacPRO

Table 1/1

Catalog Number	Package Quantity	Rack Width	Certifications	Quick Ship
20860-107	1	84HP	RoHS	No
20860-108	1	84HP	RoHS	No
20860-109	1	84HP	RoHS	No
20860-110	1	84HP	RoHS	No

Catalog Number	Package Quantity	Rack Width	Certifications	Quick Ship
20860-111	1	84HP	RoHS	No
20860-112	1	84HP		No

ADDITIONAL PRODUCT DETAILS

Mounting plates can also be fitted at the same time as the internal mounting for euroboards.

Where a mounting plate is used the clear mounting height is reduced by at least 2.5 mm.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE