

TT1100-OHP-THIN Water Sensing Cable for Insulated Pipe, Modular



nVent RAYCHEM TraceTek TT1100-OHP-THIN is a range of fixed length, small diameter water sensing cables for use on insulated pipes.

FEATURES

Advanced technology: supplied with a porous fluoropolymer outer fiber braid surrounding the base TT1100 sensor cable

Simple and fast to install: the fiber overbraid provides superior flexibility, with factory fitted plastic connectors

Easy to design: modular, fixed lengths

Mechanically strong: fluoropolymer outer braid withstands compression forces associated with the use of sheet metal lagging surrounding the pipe insulation

SPECIFICATIONS

Outer Diameter:	0.27 in
Max Operating Temperature:	176 °F
Detection Method:	Raychem Conductive-Polymer Technology
Model:	Sensing Cable
Detection:	Water

Table 1/1

Catalog Number	Item Name	Length
P000001254	TT1100-OHP-THIN-15M-PC	50 ft
P000001257	TT1100-OHP-THIN-1M-PC	3 ft
P000001251	TT1100-OHP-THIN-100M-PC	328 ft

Catalog Number	Item Name	Length
P000001255	TT1100-OHP-THIN-7.5M-PC	25 ft
P000001253	TT1100-OHP-THIN-30M-PC	100 ft
P000001256	TT1100-OHP-THIN-3M-PC	10 ft
P000001252	TT1100-OHP-THIN-50M-PC	165 ft

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT