


Novastar Base Plate, Heavy-Duty



Base plate is a plain steel blanking plate fitted to the cabinet base. Restricts air-flow into the cabinet from floor cavity and can be opened for cable ducting.

CERTIFICATIONS



FEATURES

Heavy-load floor panel

Load-carrying capacity 50 kg (110 lb)

Cutout for cable ducting

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Steel

Table 1/1

Catalog Number	Package Quantity	Color	Color Code	Finish	Type	Quick Ship
25230-149	1	Black Grey	RAL 7021	Powder Coated	Base Plate	No
25230-153	1	Black Grey	RAL 7021	Powder Coated	Base Plate	No
25230-152	1	Black Grey	RAL 7021	Powder Coated	Base Plate	No

CatalogNumber	Package Quantity	Color	Color Code	Finish	Type	Quick Ship
25230-151	1	Black Grey	RAL 7021	Powder Coated	Base Plate	No
25230-150	1	Black Grey	RAL 7021	Powder Coated	Base Plate	No

ADDITIONAL PRODUCT DETAILS

Please order brush strip separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE