


# Plug-In Unit U-Profile Front Panel for Handle Form 1



U-profile front panel. Enables the assembly of form 1 trapezoid form extraction handle. The front panel can be shielded with a textile gasket.

## CERTIFICATIONS



## FEATURES

Al profile, front anodized, rear conductive

Front panel, U-profile, shieldable

Alignment pin pressed-in, stainless steel

## SPECIFICATIONS

<b>Material:</b>	Aluminum
<b>Finish:</b>	Anodized; Passivated
<b>Accessory Type:</b>	Front panel
<b>Product Type:</b>	Front Panel
<b>Type:</b>	Front Panel with Handle (PIU)
<b>EMC Shielding:</b>	No (Retrofittable)

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	EMC Gasket Type
----------------	-------------	------------	------------------	-------------	----------	-----------------

30848-461	3U	4HP	1	Trapezoid, Type 1	Screw-on Front	Textile
30848-463	3U	6HP	1	Trapezoid, Type 1	Screw-on Front	Textile
30848-465	3U	8HP	1	Trapezoid, Type 1	Screw-on Front	Textile
30848-466	3U	10HP	1	Trapezoid, Type 1	Screw-on Front	Textile
30848-467	3U	12HP	1	Trapezoid, Type 1	Screw-on Front	Textile
30848-468	6U	4HP	1	Trapezoid, Type 1	Screw-on Front	Textile
30848-470	6U	6HP	1	Trapezoid, Type 1	Screw-on Front	Textile
30848-472	6U	8HP	1	Trapezoid, Type 1	Screw-on Front	Textile
30848-473	6U	10HP	1	Trapezoid, Type 1	Screw-on Front	Textile
30848-474	6U	12HP	1	Trapezoid, Type 1	Screw-on Front	Textile

Table 2/2

Catalog Number	Front Finish	Rear Finish	Treated Edges	Complies With	Quick Ship
30848-461	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No
30848-463	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No
30848-465	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No
30848-466	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No
30848-467	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No
30848-468	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No
30848-470	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No
30848-472	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No


Catalog Number	Front Finish	Rear Finish	Treated Edges	Complies With	Quick Ship
30848-473	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No
30848-474	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No

## ADDITIONAL PRODUCT DETAILS

Please order EMC profile seal separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**