

Thermoelectric Coolers Indoor/Outdoor



Thermoelectric Coolers minimize downtime and component loss by removing heat around critical components within an enclosure. These compact, low-profile coolers using the Peltier effect allow for cooling of small indoor and outdoor enclosures. No condensers, compressors or filters are required making it a reliable solution for demanding low-maintenance environments and low noise.

Operates on the Peltier effect for cooling or heating

INDUSTRY STANDARDS

UR, cUR Recognized; Type 12, 3R, 4, 4X; File No. SA6453

CE

IP 65

FEATURES

Operates on the Peltier effect for cooling or heating

Contains no refrigerant, making it earth friendly

Filterless design reduces maintenance requirements

Compressor-free air conditioning for demanding indoor and outdoor applications

Prewired with simple terminal block for easy wiring connections

Shrouded and unshrouded models included in standard packages

Operating temperature range -40 C (-40 F) to 55 C (131 F)

Partial recess mount

DC Powered operation for 24V and 48V applications

Low profile design allows for mounting vertically and horizontally on any enclosure to avoid interference with internal components

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Height	Width	Depth	Nominal Voltage	Nominal Capacity Btu/h
TE090624010	21074	9.29in	5.02in	6.94in	24V	178Btu/h
TE090624011	21076	9.29in	5.02in	6.94in	24V	178Btu/h

CatalogNumber	Article Number	Height	Width	Depth	Nominal Voltage	Nominal Capacity Btu/h
TE090624020	21065	9.06in	4.84in	6.91in	24V	178Btu/h
TE121024010	21075	12in	6.18in	7.43in	24V	321Btu/h
TE121024011	21072	12in	6.18in	7.43in	24V	321Btu/h
TE121024020	21066	11.81in	6.02in	7.4in	24V	321Btu/h
TE121048010	21071	12in	6.18in	7.43in	48V	321Btu/h
TE121048020	20812	11.81in	6.02in	7.4in	48V	321Btu/h
TE162024010	21077	15.93in	7.35in	7.27in	24V	567Btu/h
TE162024011	21067	15.93in	7.35in	7.27in	24V	567Btu/h
TE162024020	21068	15.75in	7.09in	7.25in	24V	567Btu/h
TE162048010	21073	15.93in	7.35in	7.27in	48V	567Btu/h
TE162048020	21064	15.75in	7.09in	7.25in	48V	567Btu/h

Table 2/3						
Catalog Number	Article Number	Nominal Capacity Watts	Voltage DC	Max Current	Operating Temperature	Material
TE090624010	21074	52W	18V	4.4A	-40 to 131°F	Mild Steel
TE090624011	21076	52W	18V	4.4A	-40 to 131°F	Stainless Steel 304
TE090624020	21065	52W	18V	4.4A	-40 to 131°F	Aluminum
TE121024010	21075	94W	18V	8.5A	-40 to 131°F	Mild Steel
TE121024011	21072	94W	18V	8.5A	-40 to 131°F	Stainless Steel 304

CatalogNumber	Article Number	Nominal Capacity Watts	Voltage DC	Max Current	Operating Temperature	Material
TE121024020	21066	94W	18V	8.5A	-40 to 131°F	Aluminum
TE121048010	21071	94W	40V	4.4A	-40 to 131°F	Mild Steel
TE121048020	20812	94W	40V	4.4A	-40 to 131°F	Aluminum
TE162024010	21077	166W	18V	14.7A	-40 to 131°F	Mild Steel
TE162024011	21067	166W	18V	14.7A	-40 to 131°F	Stainless Steel 304
TE162024020	21068	166W	18V	14.7A	-40 to 131°F	Aluminum
TE162048010	21073	166W	40V	7.6A	-40 to 131°F	Mild Steel
TE162048020	21064	166W	40V	7.6A	-40 to 131°F	Aluminum

Table 3/3

Catalog Number	Article Number	Finish	Color	Color Code	Thickness	Quick Ship
TE090624010	21074	Powder Coated	Light Gray	RAL 7035	16ga	No
TE090624011	21076	Brushed #4			16ga	No
TE090624020	21065	Anodized			16ga	No
TE121024010	21075	Powder Coated	Light Gray	RAL 7035	16ga	Yes
TE121024011	21072	Brushed #4			16ga	No
TE121024020	21066	Anodized			16ga	No
TE121048010	21071	Powder Coated	Light Gray	RAL 7035	16ga	No
TE121048020	20812	Anodized			16ga	No

CatalogNumber	Article Number	Finish	Color	Color Code	Thickness	Quick Ship
TE162024010	21077	Powder Coated	Light Gray	RAL 7035	16ga	No
TE162024011	21067	Brushed #4			16ga	No
TE162024020	21068	Anodized			16ga	No
TE162048010	21073	Powder Coated	Light Gray	RAL 7035	16ga	No
TE162048020	21064	Anodized			16ga	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE