

# nVent ERIFLEX Flexbus Conductor

## Power Utilities



nVent ERIFLEX Flexbus Conductor is ready-to-use from one side with direct connection to busbar or circuit-breaker palm. It is an innovative and patented connection solution between two pieces of electrical equipment (such as a transformer, switchboard or generator). Flexbus Advanced maintains a high level of reliability and creates an easy and customizable connection on-site without additional design study, specific specialized workforce or expensive tools. The Flexbus Conductor is insulated with a low-smoke, halogen-free, flame-retardant (LSHFFR), high-temperature and class II material. Flexbus Conductor is a flexible, copper-plated, aluminum flat braid with insulation available from 2 to 10 meters length and under different cross section for 500A to 4500A applications. It allows for connection from the power supply to switchgear with only one conductor per phase up to 1600kVA and with two conductors per phase up to 3150kVA.

### CERTIFICATIONS



### FEATURES

Flexible insulated copper-plated, aluminum flat braid

Better current/ampacity than cable due to skin effect

Much more flexible than cable

No bending radius to respect

Ready-to-use from one side with direct connection on busbar or circuit breaker palm

Only one conductor per phase from 400kVA (560 A) to 1600kVA (2250 A) and two conductors per phase for 2000kVA (2800 A) to 3150kVA (4435 A)

### SPECIFICATIONS

Table 1/5

| Catalog Number      | Article Number | Length 1 (L1) | Length 2 (L2) | Connector Finish | Insulation Elongation | Insulation Thickness |
|---------------------|----------------|---------------|---------------|------------------|-----------------------|----------------------|
| FLEXCOND128<br>OL10 | 508058         | 10,000 mm     | 100 mm        | Tinned           | 500 % Min             | 2.5 – 3.5 mm         |

Table 2/5

| Catalog Number      | Article Number | Dielectric Strength | Euroclass CPR    | Halogen Free Rating                        | Low Smoke Rating                         | Mechanical Resistance Rating |
|---------------------|----------------|---------------------|------------------|--------------------------------------------|------------------------------------------|------------------------------|
| FLEXCOND128<br>OL10 | 508058         | 20 kV/mm            | Eca - s2, d2, a3 | UL® 2885,<br>IEC® 60754-1,<br>IEC® 62821-2 | IEC® 61034-2,<br>ISO 5659-2,<br>UL® 2885 | IK09                         |

Table 3/5

| Catalog Number      | Article Number | UV Resistance Rating                     | Nominal Voltage, IEC    | Working Temperature | ΔT 60 K | Width 1 (W1) |
|---------------------|----------------|------------------------------------------|-------------------------|---------------------|---------|--------------|
| FLEXCOND128<br>OL10 | 508058         | UL® 2556, UL® 854, IEC® 60364: AN3 Level | 1,000 VAC,<br>1,500 VDC | -50 to 115 °C       | 1,984 A | 108 mm       |

Table 4/5

| Catalog Number      | Article Number | Width 2 (W2) | Height 1 (H1) | Height 2 (H2) | Unit Weight | A     |
|---------------------|----------------|--------------|---------------|---------------|-------------|-------|
| FLEXCOND128<br>OL10 | 508058         | 100 mm       | 31.1 mm       | 18 mm         | 56.800 kg   | 50 mm |

Table 5/5

| Catalog Number      | Article Number | B     | C     | D     | 2 Bar Current Coefficient, Non-Symmetric | 2 Bar Current Coefficient, Symmetric |
|---------------------|----------------|-------|-------|-------|------------------------------------------|--------------------------------------|
| FLEXCOND128<br>OL10 | 508058         | 50 mm | 25 mm | 25 mm | 1.48                                     | 2                                    |

**Installation  
Standard:**


AS 3008;BS 7671;CEI 64-8;CSN;DIN VDE 0100;HD 384;IEC® 60364;NBR 5410;NEN 1010;NFC 15-100;NIBT-NIN;NP (2002);ÖNORM;REBT;RGIE-AREI

## ADDITIONAL PRODUCT DETAILS

Optional extender available for more connection possibilities.

| Current Coefficient According to Temperature Rise |                                |                                |                                |                                |                                |                                |                                |                                |
|---------------------------------------------------|--------------------------------|--------------------------------|--------------------------------|--------------------------------|--------------------------------|--------------------------------|--------------------------------|--------------------------------|
| Temperature Rise                                  | $\Delta T\ 30^{\circ}\text{C}$ | $\Delta T\ 40^{\circ}\text{C}$ | $\Delta T\ 45^{\circ}\text{C}$ | $\Delta T\ 50^{\circ}\text{C}$ | $\Delta T\ 55^{\circ}\text{C}$ | $\Delta T\ 60^{\circ}\text{C}$ | $\Delta T\ 65^{\circ}\text{C}$ | $\Delta T\ 70^{\circ}\text{C}$ |
| Derating Coefficient                              | 0.71                           | 0.82                           | 0.87                           | 0.91                           | 0.96                           | 1.00                           | 1.04                           | 1.08                           |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE