

MI Series Inconel 600 HIQ Heating Cable



nVent RAYCHEM HIQ Inconel 600 sheathed mineral insulated (MI) series resistance trace heating cables provide freeze protection and process temperature maintenance. They can be used for exposure temperatures up to 700 °C (joint dependent) and typical power outputs up to 300 W/m. Alloy 600 sheath offers excellent corrosion resistance to a wide range of organic acids, alkalis and chloride stress-corrosion cracking. Approved for use in hazardous areas. Available 'fast track' as configured heating units.

CARACTERÍSTICAS

Reduced total installed cost

Reduced power supply costs: lower start up currents compared with other technologies

Simple controls: current monitoring on series resistance provides instant visibility on critical circuits

Fast track/expedited service for configured heating units for eligible designs

Standard 550 °C continuous withstand temperature, with braze weld technology

Optional 700 °C continuous withstand temperature, with laser welded technology

Excellent corrosion resistance to a wide range of organic acids, alkalis and chloride stress-corrosion cracking

ESPECIFICACIONES

Min Cable Spacing:	25 mm
Max Power Output:	300 W/m
Max Continuous Exposure Temperature, Power Off:	680 °C
Temperatura de instalación mín.:	-60 °C
Supply Voltage:	0 – 500 V
Area Classification:	Non-Hazardous; Hazardous
Sheath Material:	Inconel 600
Material aislante:	Magnesium Oxide

Table 1/1

Número de catálogo	Nominal Resistance @ 20°C	Diámetro exterior
HIQ1M10K	10000 Ω/km	3.2 mm

Número de catálogo	Nominal Resistance @ 20°C	Diámetro exterior
HIQ1M4000	4000 Ω/km	3.2 mm
HIQ1M6300	6300 Ω/km	3.2 mm
HIQ1M2500	2500 Ω/km	3.4 mm
HIQ1M1600	1600 Ω/km	3.6 mm
HIQ1M1000	1000 Ω/km	3.9 mm
HIQ1M160	160 Ω/km	6.5 mm
HIQ1M630	630 Ω/km	4.3 mm
HIQ1M400	400 Ω/km	4.7 mm
HIQ1M250	250 Ω/km	5.3 mm

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT