

# Air Terminal Base, Horizontal Mount, Imperial Thread

## Power Utilities



### CARACTERÍSTICAS

Can be fastened mechanically or bonded using hot pitch, roofing compound or commercial adhesive on built-up roof surfaces or other location where holes cannot be made


Positive single bolt tension for multi-directional cable clamping

### ESPECIFICACIONES

Table 1/1

| Número de catálogo | Tamaño del conductor, UL     | Altura (H) | Anchura (W) | Peso por unidad |
|--------------------|------------------------------|------------|-------------|-----------------|
| LPA30912           | Clase 1 - Clase 2 (4/0 máx.) | 20.64 mm   | 101.600 mm  | 0.141 kg        |

## DIAGRAMAS



## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

©2025 nVent. Todas las marcas y logotipos de nVent son propiedad de nVent Services GmbH o sus filiales, o se utilizan bajo su licencia. El resto de las marcas comerciales son propiedad de sus respectivos propietarios. nVent se reserva el derecho a cambiar las especificaciones sin previo aviso.

Este documento lo ha generado el sistema.