

Front Panel, U-profile, Refrofit Shielding

Servicios públicos de energía



U-profile front panel for textile EMC gasket.

CERTIFICACIONES



CARACTERÍSTICAS

U-profile, front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Rack Width	Package Quantity	Montaje	EMC Gasket Type	Front Finish
20848-047	3 U	42 HP	1	Screw-on Front	Textile	Anodizado
20848-068	3 U	63 HP	1	Screw-on Front	Textile	Anodizado

Número de catálogo	Rack Height	Rack Width	Package Quantity	Montaje	EMC Gasket Type	Front Finish
20848-097	3 U	84 HP	1	Screw-on Front	Textile	Anodizado
20848-139	6 U	42 HP	1	Screw-on Front	Textile	Anodizado
20848-160	6 U	63 HP	1	Screw-on Front	Textile	Anodizado
20848-189	6 U	84 HP	1	Screw-on Front	Textile	Anodizado
20848-260	2 U	42 HP	1	Screw-on Front	Textile	Anodizado
20848-261	2 U	63 HP	1	Screw-on Front	Textile	Anodizado
20848-262	2 U	84 HP	1	Screw-on Front	Textile	Anodizado
20848-268	4 U	28 HP	1	Screw-on Front	Textile	Anodizado
20848-269	4 U	42 HP	1	Screw-on Front	Textile	Anodizado
20848-270	4 U	42 HP	1	Screw-on Front	Textile	Anodizado
20848-271	4 U	84 HP	1	Screw-on Front	Textile	Anodizado
20848-280	9 U	84 HP	1	Screw-on Front	Textile	Anodizado
20848-648	5 U	42 HP	1	Screw-on Front	Textile	Anodizado
20848-649	5 U	63 HP	1	Screw-on Front	Textile	Anodizado
20848-650	5 U	84 HP	1	Screw-on Front	Textile	Anodizado
30849-001	3 U	2 HP	5	Screw-on Front	Textile	Anodizado
30849-002	6 U	2 HP	5	Screw-on Front	Textile	Anodizado
20848-013	3 U	14 HP	5	Screw-on Front	Textile	Anodizado

Número de catálogo	Rack Height	Rack Width	Package Quantity	Montaje	EMC Gasket Type	Front Finish
20848-015	3 U	16 HP	5	Screw-on Front	Textile	Anodizado
20848-020	3 U	21 HP	5	Screw-on Front	Textile	Anodizado
20848-027	3 U	28 HP	5	Screw-on Front	Textile	Anodizado
30848-354	3 U	4 HP	5	Screw-on Front	Textile	Anodizado
30848-356	3 U	8 HP	5	Screw-on Front	Textile	Anodizado
30848-358	3 U	12 HP	5	Screw-on Front	Textile	Anodizado
30848-378	3 U	5 HP	5	Screw-on Front	Textile	Anodizado
30848-380	3 U	6 HP	5	Screw-on Front	Textile	Anodizado
30848-382	3 U	7 HP	5	Screw-on Front	Textile	Anodizado
30848-386	3 U	10 HP	5	Screw-on Front	Textile	Anodizado
30849-004	3 U	3 HP	5	Screw-on Front	Textile	Anodizado
30848-355	6 U	4 HP	5	Screw-on Front	Textile	Anodizado
30848-379	6 U	5 HP	5	Screw-on Front	Textile	Anodizado
20848-106	6 U	14 HP	5	Screw-on Front	Textile	Anodizado
20848-108	6 U	16 HP	5	Screw-on Front	Textile	Anodizado
20848-113	6 U	21 HP	5	Screw-on Front	Textile	Anodizado
20848-120	6 U	28 HP	5	Screw-on Front	Textile	Anodizado
30848-357	6 U	8 HP	5	Screw-on Front	Textile	Anodizado

Número de catálogo	Rack Height	Rack Width	Package Quantity	Montaje	EMC Gasket Type	Front Finish
30848-359	6 U	12 HP	5	Screw-on Front	Textile	Anodizado
30848-381	6 U	6 HP	5	Screw-on Front	Textile	Anodizado
30848-383	6 U	7 HP	5	Screw-on Front	Textile	Anodizado
30848-387	6 U	10 HP	5	Screw-on Front	Textile	Anodizado

Table 2/3						
Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
20848-047	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-068	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-097	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-139	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-160	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-189	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-260	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	84 mm	Aluminio
20848-261	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	84 mm	Aluminio
20848-262	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	84 mm	Aluminio
20848-268	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminio

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
20848-269	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminio
20848-270	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminio
20848-271	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminio
20848-280	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	395.1 mm	Aluminio
20848-648	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	217.4 mm	Aluminio
20848-649	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	217.4 mm	Aluminio
20848-650	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	217.4 mm	Aluminio
30849-001	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
30849-002	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-013	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-015	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-020	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-027	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
30848-354	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
30848-356	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
30848-358	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
30848-378	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
30848-380	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
30848-382	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
30848-386	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
30849-004	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
30848-355	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
30848-379	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-106	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-108	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-113	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-120	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
30848-357	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
30848-359	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
30848-381	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
30848-383	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
30848-387	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio

Table 3/3

Número de catálogo	Product Type	Tipo	Ancho	Certificaciones
20848-047	Front Panel	Front Panel without Handle	213 mm	RoHS
20848-068	Front Panel	Front Panel without Handle	319.7 mm	RoHS
20848-097	Front Panel	Front Panel without Handle	426.4 mm	RoHS
20848-139	Front Panel	Front Panel without Handle	213 mm	RoHS
20848-160	Front Panel	Front Panel without Handle	319.7 mm	RoHS
20848-189	Front Panel	Front Panel without Handle	426.4 mm	RoHS
20848-260	Front Panel	Front Panel without Handle	213 mm	
20848-261	Front Panel	Front Panel without Handle	319.7 mm	
20848-262	Front Panel	Front Panel without Handle	426.4 mm	RoHS
20848-268	Front Panel	Front Panel without Handle	141.9 mm	RoHS
20848-269	Front Panel	Front Panel without Handle	213 mm	RoHS
20848-270	Front Panel	Front Panel without Handle	213 mm	RoHS

Número de catálogo	Product Type	Tipo	Ancho	Certificaciones
20848-271	Front Panel	Front Panel without Handle	426.4 mm	RoHS
20848-280	Front Panel	Front Panel without Handle	426.4 mm	RoHS
20848-648	Front Panel	Front Panel without Handle	213 mm	
20848-649	Front Panel	Front Panel without Handle	319.7 mm	
20848-650	Front Panel	Front Panel without Handle	426.4 mm	
30849-001	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30849-002	Front Panel	Front Panel without Handle	9.8 mm	RoHS
20848-013	Front Panel	Front Panel without Handle	70.8 mm	RoHS
20848-015	Front Panel	Front Panel without Handle	80.9 mm	RoHS
20848-020	Front Panel	Front Panel without Handle	106.3 mm	RoHS
20848-027	Front Panel	Front Panel without Handle	141.9 mm	RoHS
30848-354	Front Panel	Front Panel without Handle	20 mm	RoHS
30848-356	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30848-358	Front Panel	Front Panel without Handle	60.6 mm	RoHS
30848-378	Front Panel	Front Panel without Handle	25 mm	RoHS
30848-380	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30848-382	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30848-386	Front Panel	Front Panel without Handle	50.5 mm	RoHS

Número de catálogo	Product Type	Tipo	Ancho	Certificaciones
30849-004	Front Panel	Front Panel without Handle	14.9 mm	RoHS
30848-355	Front Panel	Front Panel without Handle	20 mm	RoHS
30848-379	Front Panel	Front Panel without Handle	25 mm	RoHS
20848-106	Front Panel	Front Panel without Handle	70.8 mm	RoHS
20848-108	Front Panel	Front Panel without Handle	80.9 mm	RoHS
20848-113	Front Panel	Front Panel without Handle	106.3 mm	RoHS
20848-120	Front Panel	Front Panel without Handle	141.9 mm	RoHS
30848-357	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30848-359	Front Panel	Front Panel without Handle	60.6 mm	RoHS
30848-381	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30848-383	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30848-387	Front Panel	Front Panel without Handle	50.5 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

14 ... 84 HP: multi-part U-profile (front panel with crimped profiles).

Differences in finish between 2 ... 12 HP and 14 ... 84 HP.

2 ... 12 HP: one-part U-profile

Please order textile EMC gasket separately.

Standard pack quantity: 2 to 28HP: 5 pieces, 42 to 84 HP: 1 piece, supplied in standard pack quantities (SPQ) only.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de

atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE