

TT1100-OHP-THIN Water Sensing Cable for Insulated Pipe, Modular



nVent RAYCHEM TraceTek TT1100-OHP-THIN is a range of fixed length, small diameter water sensing cables for use on insulated pipes.

CARACTERÍSTICAS

Advanced technology: supplied with a porous fluoropolymer outer fiber braid surrounding the base TT1100 sensor cable

Simple and fast to install: the fiber overbraid provides superior flexibility, with factory fitted plastic connectors

Easy to design: modular, fixed lengths

Mechanically strong: fluoropolymer outer braid withstands compression forces associated with the use of sheet metal lagging surrounding the pipe insulation

ESPECIFICACIONES

Diámetro exterior:	6,8 mm
Max Operating Temperature:	80 °C
Detection Method:	Raychem Conductive-Polymer Technology
Model:	Sensing Cable
Detection:	Water

Table 1/1

Número de catálogo	Nombre del artículo	Longitud
P000001251	TT1100-OHP-THIN-100M-PC	100 m
P000001252	TT1100-OHP-THIN-50M-PC	50 m
P000001253	TT1100-OHP-THIN-30M-PC	30 m

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT