

nVent ERICO Ericore Underminated Conductor

Power Utilities



CARACTERÍSTICAS

Low-inductance, low-impedance cable designed to minimize voltage build-up due to lightning impulses

Multiple insulated layers of conductor reduce the potential of side flashing

Requires upper and lower termination kits

ESPECIFICACIONES

Table 1/1

Número de catálogo	Capacitancia	Impedancia	Inductancia	Resistencia (Rdc)	Resistencia (Rimp)	Peso por unidad
ERICORE001U	0.75 pF	12 Ω Max	37 nH	0.500 m Ω /m	6 m Ω /m	1.180 kg

DETALLES ADICIONALES DEL PRODUCTO

Consult nVent ERICO technical support or the installation manual for guidance on maximum allowable lengths.

Inductance and Capacitance are per meter.

DIAGRAMAS



ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte