

C13 Weldable Half Coupler



CERTIFICATIONS



FONCTIONS

Designed for connecting reinforcing bar perpendicular to structural steel sections or plates

Internally taper threaded on one end, with the other end prepared for welding

Machined from weldable grades of steel

Slim design maintains concrete cover

SPÉCIFICATIONS

Finition: Brut

Matériau: Acier

Table 1/2

Référence catalogue	Taille de barre d'armature, métrique	Taille de barre d'armature, US	Taille de barre d'armature, Canada	Diamètre 1 (Ø1)	Diamètre 2 (Ø2)	Longueur (L)
EL12C13N	12 mm	#4	10M	20 mm	11 mm	40mm
EL16C13N	16 mm	#5	15M	25 mm	18 mm	45mm

Référence catalogue	Taille de barre d'armature, métrique	Taille de barre d'armature, US	Taille de barre d'armature, Canada	Diamètre 1(Ø1)	Diamètre 2(Ø2)	Longueur (L)
EL14C13N	14 mm			25 mm	18 mm	42mm
EL18C13N	18 mm			30 mm	24 mm	50mm
EL20C13N	20 mm	#6	20M	30 mm	22 mm	59mm
EL22C13N	22 mm	#7		35 mm	16 mm	65mm
EL28C13N	28 mm	#9	30M	40 mm	16 mm	74mm
EL25C13N	25 mm	#8	25M	40 mm	24 mm	68mm
EL36C13N	36 mm	#11	35M	50 mm	22 mm	87mm
EL32C13N	32 mm	#10		50 mm	32 mm	75mm
EL43TC13N	43 mm	#14	45M	60 mm	25 mm	110mm
EL50TC13N	50 mm			70 mm	29 mm	117mm
EL38C13N	38 mm			60 mm	38 mm	85mm
EL40C13N	40 mm			60 mm	32 mm	91mm
EL57TC13N	57 mm	#18	55M	80 mm	32 mm	133mm

Table 2/2

Référence catalogue	Profondeur de barre (BD)	Poids unitaire	Certifications
EL12C13N	19mm	0.06 kg	RISE
EL16C13N	24mm	0.11 kg	RISE
EL14C13N	21mm	0.12 kg	RISE


Référence catalogue	Profondeur de barre (BD)	Poids unitaire	Certifications
EL18C13N	29mm	0.2 kg	
EL20C13N	35mm	0.22 kg	RISE
EL22C13N	37mm	0.32 kg	
EL28C13N	42mm	0.41 kg	
EL25C13N	40mm	0.45 kg	RISE
EL36C13N	52mm	0.74 kg	
EL32C13N	45mm	0.75 kg	RISE
EL43TC13N	66mm	1.37 kg	
EL50TC13N	70mm	1.94 kg	
EL38C13N	53mm	1.24 kg	
EL40C13N	57mm	1.25 kg	RISE
EL57TC13N	83mm	2.92 kg	

INFORMATIONS PRODUIT COMPLÉMENTAIRES

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

The design of the weld, the selection of electrode, and other relevant choices depend on the chemical and physical properties of the structural steel to which the couplers are welded. Engineers who design assemblies should adhere to all appropriate regulations.

DIAGRAMMES



AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Notre gamme complète de marques:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE