

# 19" Pusher Fan, 2 U, Axial

## Centrale d'électricité

Fan tray with integrated pusher fan.



### CERTIFICATIONS



### CARACTÉRISTIQUES

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to sub racks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

### LES CARACTÉRISTIQUES TECHNIQUES

Table 1/1

| Référence catalogue | Input Voltage AC | Input Voltage DC |
|---------------------|------------------|------------------|
| 10713-518           | 230 V min        |                  |
| 10713-520           | 115 V min        |                  |

| Référence catalogue | Input Voltage AC | Input Voltage DC |
|---------------------|------------------|------------------|
| 10713-526           | 230 V min        |                  |
| 10713-534           | 230 V min        |                  |
| 10713-536           | 115 V min        |                  |
| 10713-529           |                  | 24 V min         |
| 10713-537           |                  | 24 V min         |
| 19713-540           |                  |                  |

## ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**