

Straight Through Joint



nVent PYROTENAX Straight Through Joint - NAM are a range of field installed, non fire-rated splice kits used to join MI copper-sheathed cables (with up to seven conductors), either where the manufactured length is shorter than the run length or for repair of damaged cables. If moisture is present, it must also be protected with a moisture protection kit.

CARACTÉRISTIQUES

Installation simple

Fiabilité et longue durée de vie : 30 year product warranty available

LES CARACTÉRISTIQUES TECHNIQUES

Tension nominale: 600 V

Matériau: Laiton

Table 1/1

Référence catalogue	Température maxi de service	Convient pour le type de câble
STJ2/18-215T	105 °C	2/18-215T
STJ2/18-324TS	105 °C	2/18-324TS
STJ2/16-246T	105 °C	2/16-246T
STJ2/16-340	105 °C	2/16-340
STJ2/16-364TS	105 °C	2/16-364TS
STJ3/16-355	105 °C	3/16-355

Référence catalogue	Température maxi de service	Convient pour le type de câble
STJ4/16-387	105 °C	4/16-387
STJ2/14-371	105 °C	2/14-371
STJ3/14-387	105 °C	3/14-387
STJ4/14-465	105 °C	4/14-465
STJ7/14-496	105 °C	7/14-496
STJ2/12-402	105 °C	2/12-402
STJ3/12-480	105 °C	3/12-480
STJ4/12-465	105 °C	4/12-465
STJ7/12-543	105 °C	7/12-543
STJ1/10-277	90 °C	1/10-277
STJ2/10-449	105 °C	2/10-449
STJ3/10-480	105 °C	3/10-480
STJ4/10-590	105 °C	4/10-590
STJ7/10-621	105 °C	7/10-621
STJ1/8-298	90 °C	1/8-298
STJ3/8-590	105 °C	3/8-590
STJ4/8-590	105 °C	4/8-590
STJ1/6-340	90 °C	1/6-340

Référence catalogue	Température maxi de service	Convient pour le type de câble
STJ3/6-621	105 °C	3/6-621
STJ4/6-730	105 °C	4/6-730
STJ1/4-402	90 °C	1/4-402
STJ3/4-746	105 °C	3/4-746
STJ1/3-449	90 °C	1/3-449
STJ3/3-834	105 °C	3/3-834
STJ1/2-449	90 °C	1/2-449
STJ1/2-449/465	90 °C	1/2-449 to 465/1
STJ2/2-865	105 °C	2/2-865
STJ1/1-496	90 °C	1/1-496
STJ2/1-975	105 °C	2/1-975
STJ1/1/0-512	90 °C	1/1/0-512
STJ1/1/0-543/512	90 °C	1/1/0-512 to 543/1
STJ1/2/0-580	90 °C	1/2/0-580
STJ1/2/0-580/590	90 °C	1/2/0-580 to 590/1
STJ1/3/0-621	90 °C	1/3/0-621
STJ1/3/0-621/637	90 °C	1/3/0-621 to 637/1
STJ1/4/0-684	90 °C	1/4/0-684

Référence catalogue	Température maxi de service	Convient pour le type de câble
STJ1/4/0-684/699	90 °C	1/4/0-684 to 699/1
STJ4/0-699/11/4	105 °C	699/1 (4/0)
STJ1/250-746	90 °C	1/250-746
STJ1/350-834	90 °C	1/350-834
STJ1/500-1000	90 °C	1/500-1000

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.

Amérique du Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asie Pacifique

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Amérique latine

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT