

RackChiller Rear Door Cooler, Passive

Data Solutions



RackChiller Rear Door Cooler (RDC) Water Heat Exchanger is designed for managing high heat load cooling requirements within high-density server, computing and storage racks. The RDC installs on equipment racks as a separate rear door with an extra frame, enabling it to be retrofitted to existing racks. Heat dissipated by the rack equipment will be removed by a air-to-liquid heat exchanger and transfered into the facility water circuit, adding no heat to the IT room. The entire system is integrated within an aesthetically framed perforated door with protective covers to isolate the liquid source and cooling loop from the rack-mounted equipment.

CERTIFICAZIONI



CARATTERISTICHE

Fanless solution, no noise, no additional power consumption, low maintenance

Frame solution separates coil and condensate management from the rack-mounted equipment

Rear space inside the cabinet is completely available for power distribution and cable management

Easily adapts to nVent cabinets; contact nVent to request information for integrating with third party cabinet

Temperature sensors on air supply and return side

Optional control system with Modbus TCP and SNMP v2c interface

Optional water flow, pressure and temperature sensors included with the water control package allow for water monitoring and regulation according to actual heat load

Optional local display

SPECIFICHE

Table 1/2

Codice a catalogo	Tipo di prodotto	Famiglia di prodotti	Tipo	Larghezza	Profondità	Altezza
21130-805	Scambiatore di calore liquido/aria	RackChiller	Raffreddatore portiera posteriore, passivo	800mm	226mm	2450mm
21130-802	Scambiatore di calore liquido/aria	RackChiller	Raffreddatore portiera posteriore, passivo	600mm	226mm	2200mm
21130-803	Scambiatore di calore liquido/aria	RackChiller	Raffreddatore portiera posteriore, passivo	800mm	226mm	2200mm
21130-801	Scambiatore di calore liquido/aria	RackChiller	Raffreddatore portiera posteriore, passivo	800mm	226mm	2000mm
21130-804	Scambiatore di calore liquido/aria	RackChiller	Raffreddatore portiera posteriore, passivo	600mm	226mm	2450mm
21130-800	Scambiatore di calore liquido/aria	RackChiller	Raffreddatore portiera posteriore, passivo	600mm	226mm	2000mm

Table 2/2

Codice a catalogo	Fine	Materiale	Quantità imballaggio
21130-805	Verniciato a polvere	Acciaio	1
21130-802	Verniciato a polvere	Acciaio	1
21130-803	Verniciato a polvere	Acciaio	1
21130-801	Verniciato a polvere	Acciaio	1
21130-804	Verniciato a polvere	Acciaio	1
21130-800	Verniciato a polvere	Acciaio	1

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

For trouble-free operation it is recommended to use the water connection set and the optional accessories.

The cooling capacity is determined under the following conditions: delta p water: < 100 kPa; delta p air: 15 Pa; water flow temperature: 12 °C / 53.6 °F; outlet temperature 24 °C / 75.2 °F; water flow: 4.8 m³/h / 21.1 gal/min; Airflow: Depending on cooling module see Diagram Performance Map.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE