

Rail Wallmount SRW, EN50125-3 certified



Railway ready EN50125-3 vibration tested pole-mount stainless steel enclosure for integrated wayside radio, fiber splice, access point and power distribution applications.

CARATTERISTICHE

Finish: RAL 7035 powder painting UV resistant

Body: Folded and seam welded 1.5 mm/16 gauge thick stainless steel structure, pre-equipped with M8 blind rivet nuts for wall and pole mounting

Door: Corner formed in one piece, 2 mm/14 gauge stainless steel door with 180° left opening with door stopper. Right opening doors available on request

Roof: Rain & Sun hood to protect against adverse weather conditions

Lock: Swing handle with anti-vibration mechanism equipped with DIN profile half cylinder Ronis 2131A lock and Espagnolette two points locking

Cable access: Gland plate on the bottom. Cut-outs can be requested based on project specific requirements

Protection: Up to NEMA Type 12; NEMA Type 13; NEMA Type 4X; IP66; IK10

Internal accessories: Standard: Document Pocket A4; Optional: 19" uprights on the front, Mounting plate in the rear

External accessories: Optional: Lifting eyes, wall/pole mount kits

Additional information: For outdoor environments, the use of a pressure compensation breather is advised. Also in environments known for quick temperature changes, condensation should be taken into consideration. The standard RWS enclosures are delivered with 2 pressure compensation breathers. One under the hood, one on the Gland plate. The pressure compensation breathers are also IP66.

Right opening doors available on request. Gland plate cutouts can be requested based on project specific requirements.

Optional: 19" uprights on the front, Mounting plate in the rear

SPECIFICHE

Table 1/2

Codice a catalogo	Grado di protezione	È conforme a	Quantità nella confezione	Codice colore	Finitura	Materiale
-------------------	---------------------	--------------	---------------------------	---------------	----------	-----------

SRW0806021	IP66	EN 50125-3, IEC 62262, IEC 60529	1	RAL 7035	Verniciato a polvere	Acciaio inossidabile
SRW0606030	IP66	EN 50125-3, IEC 62262, IEC 60529	1	RAL 7035	Verniciato a polvere	Acciaio inossidabile
SRW0604021	IP66	EN 50125-3, IEC 62262, IEC 60529	1	RAL 7035	Verniciato a polvere	Acciaio inossidabile
SRW0606021	IP66	EN 50125-3, IEC 62262, IEC 60529	1	RAL 7035	Verniciato a polvere	Acciaio inossidabile
SRW0806030	IP66	EN 50125-3, IEC 62262, IEC 60529	1	RAL 7035	Verniciato a polvere	Acciaio inossidabile

Table 2/2

Codice a catalogo	Spedizione rapida
SRW0806021	No
SRW0606030	No
SRW0604021	No
SRW0606021	No
SRW0806030	No

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE