

# Accoppiatore a manicotto di velocità LENTONE nVent



The nVent LENTON Speed Sleeve splice is a proven, quick and economical method of making compression-only splices in steel reinforced concrete projects. The system is designed to allow compressive loads to be transferred by aligning square cut reinforcing steel bar ends.

nVent LENTON Speed Sleeve is simple and easy to install. The small dimensions of the sleeve generally eliminate the need for additional concrete cover on the reinforcing steel because the sleeve is typically thinner than the column stirrups.

## CARATTERISTICHE

Bars can be individually secured

Fast, one-man installation

Requires only a lightweight ratchet wrench to install

Can be used on bundled bars

Self supporting; no tack welding is needed

Transition splices can be made using simple adaptor inserts

## SPECIFICHE

**Fine:** Elettro galvanizzato

**Materiale:** Acciaio

Table 1/2

| Codice a catalogo | Numero articolo | Dimensione armatura, metrica | Dimensioni armatura, USA | Dimensioni armatura, Canada | Lunghezza (L) | Larghezza (W) |
|-------------------|-----------------|------------------------------|--------------------------|-----------------------------|---------------|---------------|
| RBW26810          | 145535          | 32 mm                        | # 10                     |                             | 154mm         | 67 mm         |
| RBW2687           | 145500          | 22 mm                        | # 7                      |                             | 152mm         | 64 mm         |
| RBW2686           | 145495          | 20 mm                        | # 6                      | 20 MLN                      | 154mm         | 54 mm         |

| Codice a catalogo | Numero articolo | Dimensione armatura, metrica | Dimensioni armatura, USA | Dimensioni armatura, Canada | Lunghezza (L) | Larghezza (W) |
|-------------------|-----------------|------------------------------|--------------------------|-----------------------------|---------------|---------------|
| RBW2688           | 145510          | 25 mm                        | # 8                      | 25 MLN                      | 154mm         | 55 mm         |
| RBW2689           | 145520          | 28 mm                        | #9                       | 30 MLN                      | 154mm         | 63 mm         |
| RBW26811          | 145540          | 36 mm                        | #11                      | 35 MLN                      | 203mm         | 67 mm         |
| RBW26814          |                 | 43 mm                        | #14                      | 45 MLN                      | 280mm         | 77 mm         |
| RBW26818          | 145560          | 57 mm                        | # 18                     | 55 MLN                      | 305mm         | 92 mm         |
| RBW26840MM        | 145550          | 40 mm                        |                          |                             | 280mm         | 74 mm         |
| RBW26850          | 145555          | 50 mm                        |                          |                             | 300mm         | 89 mm         |

Table 2/2

| Codice a catalogo | Numero articolo | Altezza (H) | Larghezza presa (SW) | Numero di bulloni | Peso unità |
|-------------------|-----------------|-------------|----------------------|-------------------|------------|
| RBW26810          | 145535          | 47 mm       | 16mm                 | 4                 | 0.28 kg    |
| RBW2687           | 145500          | 45 mm       | 16mm                 | 3                 | 0.53 kg    |
| RBW2686           | 145495          | 37 mm       | 16mm                 | 3                 | 0.54 kg    |
| RBW2688           | 145510          | 42 mm       | 16mm                 | 3                 | 0.59 kg    |
| RBW2689           | 145520          | 45 mm       | 16mm                 | 3                 | 0.59 kg    |
| RBW26811          | 145540          | 54 mm       | 16mm                 | 4                 | 0.91 kg    |
| RBW26814          |                 | 52 mm       | 16mm                 | 4                 | 1.38 kg    |
| RBW26818          | 145560          | 69 mm       | 16mm                 | 4                 | 2.29 kg    |
| RBW26840MM        | 145550          | 52 mm       | 16mm                 | 4                 | 1.35 kg    |

| Codice a catalogo | Numero articolo | Altezza (H) | Larghezza presa (SW) | Numero di bulloni | Peso unità |
|-------------------|-----------------|-------------|----------------------|-------------------|------------|
| RBW26850          | 145555          | 64 mm       | 16mm                 | 4                 | 1.6 kg     |


## INFORMAZIONI DI PRODOTTO AGGIUNTIVE

nVent LENTON Speed Sleeve is a compression-only splicing system. It should never be used for tension applications.

Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the installation instructions.

## SCHEMI



## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent.

Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

#### Nord America

+1.800.753.9221

Opzione 1 – Assistenza  
clienti

Opzione 2 – Assistenza  
tecnica

#### Europa

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

#### Europa

Germania:

800 1890272

altri paesi:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Il nostro straordinario portafoglio di marchi:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**