

Kit di giunzione orizzontale serie T, riempimento superiore



T-Series splice kits contain the following: Sleeve, filler material kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), pouring basin and pouring basin crucible. Splice kits are ordered based on the quantity of splices needed. Sleeves and filler material kits are one-time use parts. Pouring basins and crucibles are prorated based on their anticipated life. Ordering splice kits simplifies ordering, reduces order errors and helps ensure proper sizing of components. Kits can be ordered with longer (extended) sleeves for use when the reinforcing steel deformation pattern or spacing does not meet the minimum product specifications.

CARATTERISTICHE

Simplifies ordering

Used to splice the same diameter bars

Available with extended sleeve lengths

SPECIFICHE

Table 1/2

Codice a catalogo	Manicotto	Dimensione armatura, metrica	Dimensioni armatura, USA	Dimensioni armatura, Canada	Lunghezza 1 (L1)	Lunghezza 2 (L2)
RBT10911H	Lunghezza estesa	32 mm	# 10		260 mm	241 mm
RBT1091H	Lunghezza standard	32 mm	# 10		260 mm	229 mm
RBT4101H	Lunghezza standard	12 mm	# 4	10 MLN	260 mm	229 mm
RBT5101H	Lunghezza standard	16 mm	# 5	15 MLN	260 mm	229 mm
RBT6101H	Lunghezza standard	20 mm	# 6	20 MLN	260 mm	229 mm

Codice a catalogo	Manicotto	Dimensione armatura, metrica	Dimensioni armatura, USA	Dimensioni armatura, Canada	Lunghezza 1 (L1)	Lunghezza 2 (L2)
RBT7101H	Lunghezza standard	22 mm	# 7		260 mm	229 mm
RBT81011H	Lunghezza estesa	25 mm	# 8	25 MLN	260 mm	241 mm
RBT81012H	Lunghezza estesa	25 mm	# 8	25 MLN	260 mm	254 mm
RBT8101H	Lunghezza standard	25 mm	# 8	25 MLN	260 mm	229 mm
RBT91012H	Lunghezza estesa	28 mm	#9	30 MLN	260 mm	254 mm
RBT9101H	Lunghezza standard	28 mm	#9	30 MLN	260 mm	229 mm
RBT111011H	Lunghezza estesa	36 mm	#11	35 MLN	260 mm	267 mm
RBT11101H	Lunghezza standard	36 mm	#11	35 MLN	260 mm	254 mm
RBT14101H	Lunghezza standard	43 mm	#14	45 MLN	260 mm	254 mm
RBT1891H	Lunghezza standard	57 mm	# 18	55 MLN	260 mm	254 mm

Table 2/2				
Codice a catalogo	Lunghezza 3 (L3)	Altezza 1 (H1)	Altezza 2 (H2)	Diametro (Ø)
RBT10911H	171mm	476mm	89mm	127 mm
RBT1091H	159mm	476mm	89mm	127 mm
RBT4101H	140mm	464mm	89mm	102 mm
RBT5101H	140mm	464mm	89mm	102 mm
RBT6101H	152mm	464mm	89mm	102 mm
RBT7101H	152mm	470mm	89mm	102 mm

Codice a catalogo	Lunghezza 3 (L3)	Altezza 1 (H1)	Altezza 2 (H2)	Diametro (Ø)
RBT81011H	165mm	470mm	89mm	102 mm
RBT81012H	179mm	470mm	89mm	102 mm
RBT8101H	152mm	470mm	89mm	102 mm
RBT91012H	179mm	476mm	89mm	102 mm
RBT9101H	152mm	476mm	89mm	102 mm
RBT111011H	179mm	476mm	95mm	152 mm
RBT11101H	165mm	476mm	95mm	127 mm
RBT14101H	178mm	552mm	95mm	152 mm
RBT1891H	203mm	552mm	108mm	178 mm

INFORMAZIONI DI PRODOTTO AGGIUNTIVE


Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

All dimensions are for reference only.

Components can also be purchased separately: (1) Sleeve, (2) Filler Material Kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), (3) Pouring Basin, and (4) Pouring Basin Crucible.

Splice Kit Components							
Splice Kit	Filler Material	Packing (2 Required)	Pouring Basin Ceramic Insert and Disk	Pouring Basin Ceramic Guide Tube	Sleeve	Pouring Basin	Pouring Basin Crucible
RBT4101H	RBF40	RBS354710	RBS5037	RBS5038	RBT5101A	RBWS1467U	RBWS22774
RBT5101H	RBF40	RBS354710	RBS5037	RBS5038	RBT5101A	RBWS1467U	RBWS22774
RBT6101H	RBF50	RBS35477	RBS5037	RBS5038	RBT6101HA	RBWS1467X	RBWS22774
RBT7101H	RBF50	RBS35478	RBS5037	RBS5038	RBT7101HA	RBWS1467A	RBWS22774
RBT81011H	RBF70	RBS354710	RBS5037	RBS5038	RBT81011HA	RBWS1467C	RBWS22774
RBT81012H	RBF80	RBS354710	RBS5037	RBS5038	RBT81012HA	RBWS1467C	RBWS22774
RBT8101H	RBF55	RBS354710	RBS5037	RBS5038	RBT8101HA	RBWS1467C	RBWS22774
RBT91012H	RBF105	RBS354711	RBS5037	RBS5038	RBT91012HA	RBWS1467D	RBWS22774
RBT9101H	RBF80	RBS354711	RBS5037	RBS5038	RBT9101HA	RBWS1467D	RBWS22774
RBT10911H	RBF105	RBS354712	RBS5037	RBS5038	RBT10911HA	RBWS1500E	RBWS22775
RBT1091H	RBF90	RBS354712	RBS5037	RBS5038	RBT1091HA	RBWS1467E	RBWS22775
RBT111011H	RBF125	RBS354712	RBS5037	RBS5038	RBT111011HA	RBWS1467F	RBWS22776
RBT11101H	RBF105	RBS354712	RBS5037	RBS5038	RBT11101HA	RBWS1467F	RBWS22775
RBT14101H	RBF195	RBS354715	RBS5037	RBS5039	RBT14101HA	RBWS1467J	RBWS22776
RBT1891H	RBF270	RBS354720	RBS5037	RBS5039	RBT1891HA	RBWS1467M	RBWS22777

SCHEMI



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

Nord America

+1.800.753.9221

Opzione 1 – Assistenza
clienti

Opzione 2 – Assistenza
tecnica

Europa

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Germania:

800 1890272

altri paesi:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Il nostro straordinario portafoglio di marchi:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE