

19" Fan Unit, 1 U, Remote Control and Monitoring

Energiebedrijven

Fan Unit with ModBus interface for installation into a 1 U space within the Cabinet

KENMERKEN

Fan speed temperature controlled

ModBus Interface for Remote Monitoring and Control

Temperature threshold for the fan control adjustable on the front panel

Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs

Integrated power supply with wide range input (100 V – 240 V)

Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer

2 NTC temperature sensors with Cables included

SPECIFICATIES

Table 1/2

Catalogusnummer	Input Voltage AC	Airflow	Noise Level	Voeding	Max Static Pressure	Ambient Temperature
10713-554	100 – 240 V	1089 m³/h	59.5 dB(A)	97 W	78 Pa	–10 to 70 °C

Table 2/2

Catalogusnummer	Lifespan, L10 @ 40 C
10713-554	99558 h

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of

fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE