


Vermogenaansluitblok, Flexibar - 2 kabels, 400 A IEC, aluminium

Data Solutions

CATALOGUSNUMMER

SBF2C400AL



nVent ERIFLEX Power Blocks are the main DIN mounted output/input devices for connection between primary and secondary switchboard, or main input/output connection for machine or industrial equipment (such as inverter, air conditioning machines, etc.). The high short circuit rated large cross section blocks offer time savings and reliability in every panel configuration. The complete Power Blocks range offers multiple connection types with up to four cables, nVent ERIFLEX Flexibar Advanced, or IBSB Advanced power braids.

CERTIFICERINGEN



KENMERKEN

RoHS-conform

Halogeenvrij

Can be connected with round cross section cable or flat connection system like nVent ERIFLEX Flexibar Advanced or IBSB Advanced Insulated Braided Conductor

Compact power block with high short circuit current rating

Tinned copper or aluminum block allows for copper or aluminum conductor direct connections, or using ferrule

Screw retaining cover is hinged and removable

Design allows for visual inspection of conductor and confirmation of connection

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

Voltage detection and measurement connection

95% fill ratio

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

PRODUCTKENMERKEN

Artikelnummer: 561167

Voltooiën: Ingeblikt

Type: Flexibar-2 kabels

Standaard stroomspecificatie voor toepassingen, IEC: 400A

Materiaal: Aluminium; Thermoplastisch

Max. Geleidergrootte lijnzijde, IEC: 100 mm²

Max. Geleiderdiameter lastzijde, IEC: (2) 120 mm²

Kortstondige houdstroom (I_{cw}) 1s: 28.8kA

Max. Stroomsterkte, geïsoleerd vermogen gevlochten, IEC: 480A

Max. Stroomsterkte, nVent ERIFLEX Flexibar, IEC: 550A

Max. Stroomsterkte, UL/CSA: 335A

Piek kortsluitstroom (IPK): 51kA

Nominale voorwaardelijke kortsluitstroom (ICC): 24.3kA

Nominale kortsluitstroom (SCCR): 100kA

Max. Bedrijfsspanning, IEC (UI): 1000; 1500

Max. Bedrijfsspanning, UL (Vin): 1000

Lijnzijde aantal aansluitingen: 1

Lijnzijde geïsoleerde dwarsdoorsnede van de remkracht: 100mm²

Lijnzijde nVent ERIFLEX flexibele balkgrootte: 2x20x1 - 5x24x1

Lastzijde Compacte draadgrootte: (2) 35 - 120 mm²

Lastzijde aantal aansluitingen: 2

Draadmaat gevlochten lastzijde - ring: (2) 35 - 120 mm²

Draadgrootte lastzijde: (2) #2 – 250 kcmil

Diepte (D): 82.2mm

Hoogte (H): 146.4mm

Breedte (W): 41.5mm

Gewicht van de eenheid: 0.34kg

Certificatiegegevens: UL® 1059

Voldoet aan: IEC® 60947-7-1

Classificatie behuizing: IP 20

Brandbaar vermogen: UL® 94V-0


AANVULLENDE PRODUCTGEGEVENS

SBF250 ist UL® 1953 gelistet bei Verwendung mit SB250SPCR. Die maximale Betriebsspannung für UL-1953 Anwendungen ist 1250 VAC/DC.

Blue protection cover is less than 7% of the overall product weight.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C										
Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0,94	0,88	0,82	0,75	0,67	0,58	0,47
*environment around the terminal blocks inside the enclosure										

DIAGRAMMEN



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE