

MultipacPRO 19" Chassis, Aluminum, Plain Top and Base

Power Utilities



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

CERTIFICERINGEN



KENMERKEN

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFICATIES

Table 1/2

Catalogusnummer	Rekhoogte	Diepte	Bruikbare breedte	Montage	Volgdoet aan	EMC-afscherming
20860-601	1 U	220 mm	403 mm	Rek	IEC 60297-3-100, IEC 60297-3-105	Nee (achteraf te installeren)
20860-602	1 U	280 mm	403 mm	Rek	IEC 60297-3-100, IEC 60297-3-105	Nee (achteraf te installeren)
20860-603	1 U	340 mm	4 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-604	2 U	220 mm	4 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-605	2 U	280 mm	403 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-606	2 U	340 mm	403 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-607	3 U	280 mm	403 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-608	3 U	340 mm	403 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-609	3 U	400 mm	403 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-610	3 U	460 mm	4 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-611	4 U	280 mm	4 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-612	4 U	340 mm	403 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-613	4 U	400 mm	403 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-614	4 U	460 mm	403 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)
20860-615	5 U	460 mm	403 mm	Rek	IEC 60297-3-100	Nee (achteraf te installeren)

Table 2/2

Catalogusnummer	Productfamilie	Producttype	Type	Certificeringen
20860-601	MultipacPRO	Subrack/chassis	Vast	RoHS

Catalogusnummer	Productfamilie	Producttype	Type	Certificeringen
20860-602	MultipacPRO	Subrack/chassis	Vast	RoHS
20860-603	MultipacPRO	Subrack/chassis	Vast	
20860-604	MultipacPRO	Subrack/chassis	Vast	
20860-605	MultipacPRO	Subrack/chassis	Vast	RoHS
20860-606	MultipacPRO	Subrack/chassis	Vast	RoHS
20860-607	MultipacPRO	Subrack/chassis	Vast	RoHS
20860-608	MultipacPRO	Subrack/chassis	Vast	RoHS
20860-609	MultipacPRO	Subrack/chassis	Vast	RoHS
20860-610	MultipacPRO	Subrack/chassis	Vast	
20860-611	MultipacPRO	Subrack/chassis	Vast	
20860-612	MultipacPRO	Subrack/chassis	Vast	RoHS
20860-613	MultipacPRO	Subrack/chassis	Vast	RoHS
20860-614	MultipacPRO	Subrack/chassis	Vast	RoHS
20860-615	MultipacPRO	Subrack/chassis	Vast	RoHS

AANVULLENDE PRODUCTGEGEVENS

Please order front handles separately.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE