

# QTVR Self-Regulating Heating Cable



nVent RAYCHEM QTVR self-regulating trace heating cables are suitable for freeze protection of large pipes/vessels with high heat loss, and for process temperature maintenance applications without steam-cleaning requirements, up to 225 °F/110 °C. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

## KENMERKEN

Simplified design for hazardous areas: unconditional T4 class

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

## SPECIFICATIES

|                                                                       |                          |
|-----------------------------------------------------------------------|--------------------------|
| <b>Max Maintain or Continuous Exposure Temperature, Power On/Off:</b> | 110 °C                   |
| <b>Max Intermittent Exposure Temperature, Power On/Off:</b>           | 110 °C                   |
| <b>Supply Voltage:</b>                                                | 200 – 277 V              |
| <b>Ground Path Type:</b>                                              | Braid                    |
| <b>Outer Jacket Material:</b>                                         | Fluoropolymeer           |
| <b>Area Classification:</b>                                           | Non-Hazardous; Hazardous |

Table 1/1

| Catalogusnummer | Naam van het item | Nominal Power Output @ 10°C, 230V |
|-----------------|-------------------|-----------------------------------|
| 040615-000      | 15QTVR2-CT        | 51 W/m                            |
| 391991-000      | 10QTVR2-CT        | 38 W/m                            |
| 988967-000      | 20QTVR2-CT        | 64 W/m                            |

## WAARSCHUWING

---

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van [www.nvent.com](http://www.nvent.com) of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

### Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**