

STS MT Skin-Effect Tracing Wire



nVent RAYCHEM STS-MT Skin Effect Trace Heating Wires provide freeze protection and process temperature maintenance for embedded or long pipeline applications. Circuit lengths up to 15 miles/25 km are possible, minimizing the number of connection and power source locations. Suitable for applications up to a maximum 302 °F/150 °C and approved for use in hazardous and non-hazardous locations. The polyolefin outer jacket is ideal for heating pipelines transporting materials such as crude oil, VGO and phenol.

KENMERKEN

Custom engineered design, depending on the unique application type

Safe and efficient in operation: fully grounded system with zero electrical potential on pipe surfaces, can be used in Class 1 Division 2 and Zone 2 hazardous areas

Long circuit lengths (up to 15 miles/25 km), minimize operating and installation costs by reducing the required number of power supply points

Advanced control systems with multiple temperature inputs to adequately monitor and control longline heat tracing

Reliable during long life: entire circuit is encapsulated within rugged heat tubes and steel boxes

SPECIFICATIES

Max Power Output:	150 W/m
Max Maintain or Continuous Exposure Temperature, Power On:	150 °C
Minimale installatietemperatuur:	-55 °C
Supply Voltage:	0 – 5000 V
Area Classification:	Non-Hazardous; Hazardous
Ground Path Type:	Geen
Outer Jacket Material:	Polyolefine

Table 1/1

Catalogusnummer	Naam van het item	Nominal Cable Weight	AWG Size	Min Bending Radius @ -55°C
F74409-000	STS-MT/13.50-WIRE #6AWG	200 g/m	6	65 mm
F93310-000	STS-MT/21.50-WIRE #4AWG	300 g/m	4	72 mm

Catalogusnummer	Naam van het item	Nominal Cable Weight	AWG Size	Min Bending Radius @ -55°C
A42886-000	STS-MT/33.50-WIRE #2AWG	433 g/m	2	81 mm

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT