

Enkelt polfordelingsblokk

Data Solutions



SERTIFISERINGER



FUNKSJONER

I samsvar med RoHS

Halogen Fri

Tinned copper or aluminum block allows for copper or aluminum conductor direct connections, or using ferrule

Screw retaining cover is hinged and removable

Design allows for visual inspection of conductor and confirmation of connection

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

95% fill ratio

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

SPESIFIKASJONER

Avslutt: Tind

Table 1/2						
Katalognummer	Artikkelnummer	Maks. Strømvurdering, IEC	Maks. Strømvurdering, UL/CSA	Linjeforbindelse	Tilkopling på lastesiden	Materiale
UD-80A	569010	80A	85A	Kabel	6 kabler	Kobber, Termoplast
UDF-250A	569041	250A	255A	Flat sjåfør	6 kabler	Kobber, Termoplast
UDJ-125A	569020	125A	150A	Kabel	7 kabler	Kobber, Termoplast
UDJ-160A	569030	160A	200A	Kabel	7 kabler	Kobber, Termoplast
UD-400212AL	569251	400A	400A	2 kabler	12 kabler	Aluminium, Termoplast
UD-400112AL	569252	400A	335A	Kabel	12 kabler	Aluminium, Termoplast
UD9C630AL	569203	630A	420A	Kabel	9 kabler	Aluminium, Termoplast
UDF9C500AL	569204	500A	490A	Flat sjåfør	9 kabler	Aluminium, Termoplast
UD2C12C630AL	569205	630A	670A	2 kabler	12 kabler	Aluminium, Termoplast
UD6C500AL	569201	500A	380A	Kabel	6 kabler	Aluminium, Termoplast
UDF6C500AL	569202	500A	475A	Flat sjåfør	6 kabler	Aluminium, Termoplast
UDF12C500AL	569206	500A	500A	Flat sjåfør	12 kabler	Aluminium, Termoplast
UDF-500A	569060	500A	335A	Flat sjåfør	11 kabler	Kobber, Termoplast
UD-400212CU	569051	400A	400A	2 kabler	12 kabler	Kobber, Termoplast
UD-400112CU	569052	400A	335A	Kabel	12 kabler	Kobber, Termoplast
UD-400A	569050	400A	335A	Kabel	11 kabler	Kobber, Termoplast

Katalognummer	Artikkelnummer	Maks. Strømvurdering, IEC	Maks. Strømvurdering, UL/CSA	Linjeforbindelse	Tilkopling på lastesiden	Materiale
UD-250A	569040	250A	255A	Kabel	11 kabler	Kobber, Termoplast
UD2C12C1000AL	569207	1000A	760A	2 kabler	12 kabler	Aluminium, Termoplast
UDF12C800AL	569208	800A	670A	Flat sjåfør	12 kabler	Aluminium, Termoplast
UD2C9C1250AL	569209	1250A	950A	2 kabler	9 kabler	Aluminium, Termoplast
UDF9C1000AL	569210	1000A	840A	Flat sjåfør	9 kabler	Aluminium, Termoplast

Table 2/2						
Katalognummer	Artikkelnummer	Maks. Lederstørrelse på linje, IEC	Maks. Lederstørrelse på lasteside, IEC	Maks arbeidsspennin g, IEC (UI)	Maks. Arbeidsspennin g, UL (vin)	Sertifiseringer
UD-80A	569010	16 mm ²	16 mm ²	1000	600	CSA, cUR, RoHS, CE, ERIFLEX UD, UR
UDF-250A	569041	70 mm ²	16 mm ²	1000	600	CE, ERIFLEX UD, UR, RoHS, cUR
UDJ-125A	569020	35 mm ²	16 mm ²	1000	600	CE, ERIFLEX UD, UR, CSA, cUR, RoHS
UDJ-160A	569030	70 mm ²	16 mm ²	1000	600	RoHS, CSA, cUR, CE, ERIFLEX UD, UR
UD-400212AL	569251	95 mm ²	10 mm ²	1000, 1500	1000	CSA, cUR, RoHS, CE, ERIFLEX UD, UR
UD-400112AL	569252	185 mm ²	10 mm ²	1000, 1500	1000	CE, ERIFLEX UD, UR, RoHS, CSA, cUR
UD9C630AL	569203	300 mm ²	25 mm ²	1000, 1500	1000	UL, cUL, QPQS7.E49727 6
UDF9C500AL	569204	100 mm ²	25 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL

Katalognummer	Artikkelnummer	Maks. Lederstørrelse på linje, IEC	Maks. Lederstørrelse på lasteside, IEC	Maks arbeidsspennin g, IEC (UI)	Maks. Arbeidsspennin g, UL (vin)	Sertifiseringer
UD2C12C630AL	569205	185 mm ²	25 mm ²	1000, 1500	1000	UL, cUL, QPQS7.E49727 6
UD6C500AL	569201	240 mm ²	50 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UDF6C500AL	569202	100 mm ²	50 mm ²	1000, 1500	1000	UL, cUL, QPQS7.E49727 6
UDF12C500AL	569206	100 mm ²	25 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UDF-500A	569060	185 mm ²	35 mm ²	1000	600	cUR, RoHS, CE, ERIFLEX UD, UR
UD-400212CU	569051	95 mm ²	10 mm ²	1000, 1500	1000	CE, ERIFLEX UD, UR, RoHS, CSA, cUR
UD-400112CU	569052	185 mm ²	10 mm ²	1000, 1500	1000	CSA, cUR, CE, ERIFLEX UD, UR, RoHS
UD-400A	569050	185 mm ²	35 mm ²	1000	600	CSA, cUR, CE, ERIFLEX UD, UR, RoHS
UD-250A	569040	120 mm ²	35 mm ²	1000	600	CSA, cUR, RoHS, CE, ERIFLEX UD, UR
UD2C12C1000AL	569207	240 mm ²	25 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UDF12C800AL	569208	240 mm ²	25 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UD2C9C1250AL	569209	400 mm ²	95 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UDF9C1000AL	569210	240 mm ²	95 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL

YTTERLIGERE PRODUKTDETALJER

Increase the number of outputs with one input using a jumper on blocks with a Max Current Rating, IEC up to 160 A.

Blocks with 1,000 VAC/DC Max Working Voltage, UL are ideal for solar applications.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C										
Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell.

Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE