

IBSHY Insulated Braided Conductor for Compact Circuit Breakers

IBSHY is the ideal ready-to-install flexible wire replacement solution that is specifically designed for connections from compact molded case circuit breakers with typical current rating of 125/160 A to copper busbar . The IBSHY connects to the front access terminals of the breakers without any additional accessories, such as angular connectors, spreaders, ring terminal connectors or extenders. IBSHY is available in cross section of 32 mm² (63.15 kcmil), lengths from 230 to 830 mm (9.1" to 32.7").

Manufactured in an ISO 9001 2015 certified proprietary automated facility, IBSHY is formed by weaving high-quality electrolytic copper wire to form a durable low voltage connector with maximum flexibility that allows for more compact power connections to circuit breakers. The IBSHY allows users to reduce the total size and weight of the installation, improving both design flexibility and assembly aesthetics.

The IBSHY features integral pre-punched palms at one end with a pre-punched crimped tube at the other end both of which are ready to connect out of the box. There are no lugs to purchase or install, making connections simpler and faster and eliminating faulty connections due to vibration or fatigue.

These specific shapes give users the advantage to have the possibility to link a compact circuit breaker, or other apparatus, using connection by cage or bolt to a copper busbar with a larger bolt.

The insulation is a high-resistance, self-extinguishing, and halogen free glass fiber reinforced silicone providing possible high working temperature. IBSHY is compatible with all major brand compact molded case circuit breakers with 125/160 A nominal current. Contact your nVent ERIFLEX representative to determine the correct size for your application.



SERTIFISERINGER



FUNKSJONER

Suitable for all main 125/160 A electrical devices and specifically molded case circuit breakers

Resistant to vibration, improving reliability and performance

Improves assembly flexibility and aesthetics

Quick and easy installation

No additional cutting, stripping, crimping and punching needed

Small wire diameter provides maximum flexibility

Halogen free solution for applications requiring a low smoke solution

Conforms to NF EN 45545 obtaining an HL3 classification for chapters R22 and R23

DNV GL® certified for marine and offshore applications

High working temperature

RoHS compliant

SPESIFIKASJONER

Diameter på kabel:	0.15mm
Topp kortslutningsstrøm (Ipk):	15kA
Vanlig strømklassifisering for bruksområder:	160 A
Maks. driftsspenning, IEC (UI):	1000;1500
Overflate:	Tinnbelagt
Antennbarhetsvurdering:	UL® 1441 VW-1
Driftstemperatur:	-60 to 250 °C

Table 1/2

Katalognummer	Artikkelnummer	Materiale	Samsvarer med	Tverrsnitt	Lengde (L)	A
IBSHY32-230	558584	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439.1	32mm ²	230mm	11 mm
IBSHY32-330	558586	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439.1	32mm ²	330mm	11 mm
IBSHY32-365	558587	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439.1	32mm ²	365mm	11 mm
IBSHY32-430	558588	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439.1	32mm ²	430mm	11 mm
IBSHY32-500	558589	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439.1	32mm ²	500mm	11 mm

Katalognummer	Artikkelnummer	Materiale	Samsvarer med	Tverrsnitt	Lengde (L)	A
IBSHY32-565	558591	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439,1	32mm ²	565mm	11 mm
IBSHY32-630	558592	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439,1	32mm ²	630mm	11 mm
IBSHY32-700	558593	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439,1	32mm ²	700mm	11 mm
IBSHY32-765	558594	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439,1	32mm ²	765mm	11 mm
IBSHY32-830	558595	Copper, Glassfiberforsterket silikon	IEC® 60439.1, IEC® 61439,1	32mm ²	830mm	11 mm

Table 2/2

Katalognummer	Artikkelnummer	B	C	D	Hullstørrelse 1 (HS1)	Hullstørrelse 2 (HS2)
IBSHY32-230	558584	25 mm	3 mm	5 mm	6.5 mm	10.5 mm
IBSHY32-330	558586	25 mm	3 mm	5 mm	6.5 mm	10.5 mm
IBSHY32-365	558587	25 mm	3 mm	5 mm	6.5 mm	10.5 mm
IBSHY32-430	558588	25 mm	3 mm	5 mm	6.5 mm	10.5 mm
IBSHY32-500	558589	25 mm	3 mm	5 mm	6.5 mm	10.5 mm
IBSHY32-565	558591	25 mm	3 mm	5 mm	6.5 mm	10.5 mm
IBSHY32-630	558592	25 mm	3 mm	5 mm	6.5 mm	10.5 mm
IBSHY32-700	558593	25 mm	3 mm	5 mm	6.5 mm	10.5 mm
IBSHY32-765	558594	25 mm	3 mm	5 mm	6.5 mm	10.5 mm
IBSHY32-830	558595	25 mm	3 mm	5 mm	6.5 mm	10.5 mm

YTTERLIGERE PRODUKTDETALJER


ΔT = Temperature of conductors – Internal temperature of panel.

This table indicates the temperature rise produced by chosen current in the given section. This calculation does not take into account the heat dissipation from the switch gear.

Maximum Ampacity Ratings															
Cross Section (mm ² /kcmil)	ΔT 30° C (A)	ΔT 35° C (A)	ΔT 40° C (A)	ΔT 45° C (A)	ΔT 50° C (A)	ΔT 55° C (A)	ΔT 60° C (A)	ΔT 65° C (A)	ΔT 70° C (A)	ΔT 75° C (A)	ΔT 80° C (A)	ΔT 100° C (A)	ΔT 120° C (A)	2 Bar Current Coefficient	3 Bar Current Coefficient
32/63.15	142	153	164	174	184	193	201	209	217	225	235	263	290	1.6	2

Circuit Breaker Compatibility	
Circuit Breaker Current Rating	125/160 A
Part Number	IBSHY32x
Schneider Electric® Compact® (IEC)	NSA NG 125
Square D® PowerPact® (UL)	H-Frame
ABB® Tmax® (IEC)	T1 T2 XT1 XT2
ABB® Tmax® (UL)	T1 T2 XT1 XT2
GE® Record Plus® (IEC/UL)	FD 160
Siemens® Sentron® (IEC/UL)	VL160X 3VL1 VL160 3VL2
Moeller® xEnergy® (IEC)	NZM1
Cutler Hammer® Series G (UL)	EG Frame
Legrand® (IEC)	DPX 160 DPX3 160
Hager® (IEC)	h3 160
Rockwell/Allen Bradley (UL)	G-Frame H-Frame
OEZ (IEC)	BC160N

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk
støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE