

# Klimatyzator Extreme Environment, X



This Extreme Environments Air Conditioner is compact which is ideal for smaller depth enclosures. It supports an energy-efficient rotary compressor with a reliable smart controller. The top is sloped along with sloped internal surface reducing catchpoints for water, dust and bacteria build-up. Cutout Adapter options available for enclosures with older nVent HOFFMAN or Competitive units for easy transitions to this air conditioner.

## NORMY BRANŻOWE

UL/cUL Listed; Type 12, 4, 4X; File No. SA6453

CE

EAC

IP66/IP69/IP69K Internal Loop

IP34 External Loop

Telcordia GR-487 capable

## FUNKCJE

Energy-efficient rotary compressor

R513A or R134a refrigerant

Reliable Smart Controller on enclosure side of the unit

10-degree sloped top shroud, welded and ground

Sloped internal surfaces reduce catchpoints for water, dust, bacteria build-up

FDA-approved neoprene gasket

No louvers on vertical surfaces allow washdown with minimal protections

Cutout Adapter options for enclosures with older nVent HOFFMAN or Competitive units for easy transitions to new air conditioners

Cleanable, reusable aluminum mesh filter included to protect coils for maximum cooling performance in dirty environments

UL Listed to save customers time and money with agency approvals

Mounting hardware, gaskets and user manual furnished with the unit

Standard Air Conditioner models includes Active condensate management with heater strip, Power-off capability for door switch and other system requirements, Malfunction switch, Corrosion-resistant coating on condenser coil, Compressor heater, Head pressure control, Temperature range from -40 F/-40 C to 131 F/55 C

Manifold set ships with 2 manifolds (1x supply and 1x return) and 2 sets of mounting brackets (total of 4 brackets incl. mounting hardware)

## SPECYFIKACJE

**Wykończenie:** Szczotkowana #4  
**Materiał:** Stal nierdzewna 304

Table 1/1

| Numer katalogowy | Pojemność nominalna BTU/h | Moc nominalna w watach | Liczba faz | Wysokość (H) | Szerokość (W) | Głębokość (D) |
|------------------|---------------------------|------------------------|------------|--------------|---------------|---------------|
| X230216G160      | 2300Btu/h                 | 675W                   | 1          | 566mm        | 260mm         | 346mm         |
| X230216G170      | 2300Btu/h                 | 675W                   | 1          | 566mm        | 260mm         | 346mm         |
| X230216G360      | 2300Btu/h                 | 675W                   | 1          | 566mm        | 260mm         | 346mm         |
| X230216G370      | 2300Btu/h                 | 675W                   | 1          | 566mm        | 260mm         | 346mm         |
| X230226G160      | 1890Btu/h                 | 550W                   | 1          | 566mm        | 260mm         | 346mm         |
| X230226G170      | 1890Btu/h                 | 550W                   | 1          | 566mm        | 260mm         | 346mm         |
| X230226G360      | 1890Btu/h                 | 550W                   | 1          | 566mm        | 260mm         | 346mm         |
| X230226G370      | 1890Btu/h                 | 550W                   | 1          | 566mm        | 260mm         | 346mm         |

## SCHEMATY



## OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie [www.nvent.com](http://www.nvent.com) oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Marki w naszej ofercie:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**

©2025 nVent. Wszystkie znaki i logo nVent są własnością firmy nVent Services GmbH albo jej spółek zależnych lub są licencjonowane. Wszystkie pozostałe znaki towarowe są własnością odpowiednich właścicieli. Firma nVent zastrzega sobie prawo do zmiany specyfikacji bez powiadomienia.

Ten dokument jest generowany przez system.