

Universal Transient Barrier, Dual Pair

Power Utilities



SERTIFISERINGER



FUNKSJONER

Compact design universal transient barrier provides protection of low-voltage circuits and transducers

Separate plug and base design allows hot swappable module replacement

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions

Surge rating to 20 kA 8/20 μ s is ideal for exposed wiring


Allows for protection of 25 analog signals or 50 digital signals per linear foot (0,3 m) of DIN rail space

SPESIFIKASJONER

Katalognummer	UTB30DP
Artikkelnummer	702888
Nominell systemspenning (UN)	10 - 21 VAC 15 - 30 VDC

Katalognummer	UTB30DP
Maks. Kontinuerlig driftsspenning (UC)	23 VAC 33 VDC
Nominell laststrøm (IL)	800 mA
Frekvens	2 MHz
Sløyfemotstand	0.6 Ω
Maks utladningsstrøm (Imax), L+L-PE	20 kA 8/20 μ s
Beskyttelsesmåter	Common Differensial
Teknologi	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) SilisiumAvalanche-diode (SAD)
Spenningsbeskyttelsesnivå (opp), L-L.	44 V ved 3 Ka
Tilknytning, strandet	1 – 4 mm ²
Temperatur	-20 to 65 °C
Merkeverdi	IP 20 NEMA®-1
Høyde (H)	90 mm
Bredde (W)	12 mm
Vekt på enhet	0.090 kg
Sertifiseringsdetaljer	UL® 497B.
Erstatningsmodul	UTB30DPM

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE