

RackChiller RDHX PRO Passive, Right Hinged

Data Solutions



The new rear door cooling units from nVent are offered in a range of standard sizes for use with 42U, 47U, in both 600mm and 800mm widths (other sizes available on request). The coolers themselves are 250mm deep, with a dry weight of 140Kg. One of the features of rear door coolers is they are compact and do not require any additional floor space or ceiling headroom – in fact, their use can free up white space as CRAH units and other room cooling equipment may be eliminated from the data centre.

RDHX PRO Passive is fanless device than can be upgraded to Active with the addition of the fan modules. Meaning you can scale your data center to the requirements of your server racks. With no fans, the power consumption is near zero. This also reduces the service and maintenance costs with minimal components.

The Rear door cooler can also be retrofitted to most third party racks.

Smallest footprint of any rear door cooler on the marketplace with the highest kilowatt capacity of cooling.

FUNKCJE

Rear Door Cooler Chilled Water

Hot-swappable components simplify repair and maximize availability

Designed for efficient operation at increased facility water temperatures

Combination with direct to chip liquid cooling

Modular standard - easy to adapt to individual requirements

Can be upgraded to active even after installation and commissioning

Power supplies, controller and control valve all are hot-swappable

Automatic valve opening control

7" high resolution touch screen interface

Hydraulic and electric connection through top or bottom

Monitoring via Ethernet interface (Web browser, Modbus TCP, SNMP v2c) and Modbus RTU

SPECYFIKACJE

Table 1/3

Numer katalogowy	Typ produktu	Rodzina produktów	Wysokość stojaka	Kod koloru	Stopień ochrony	Szerokość
10630-212	Wymiennik ciepła typu powietrze-ciecz	RackChiller	42U	RAL 7021	IP20	600mm
10630-213	Wymiennik ciepła typu powietrze-ciecz	RackChiller	42U	RAL 7021	IP20	800mm
10630-214	Wymiennik ciepła typu powietrze-ciecz	RackChiller	47U	RAL 7021	IP20	600mm
10630-215	Wymiennik ciepła typu powietrze-ciecz	RackChiller	47U	RAL 7021	IP20	800mm

Table 2/3

Numer katalogowy	Głębokość	Wysokość	Napięcie zasilania	Podawanie płynu chłodzącego	Wykończenie	Materiał
10630-212	280mm	2000mm	195 – 277V	Dolne, Góra	Powłoka proszkowa	Stal
10630-213	280mm	2000mm	195 – 277V	Dolne, Góra	Powłoka proszkowa	Stal
10630-214	280mm	2200mm	195 – 277V	Dolne, Góra	Powłoka proszkowa	Stal
10630-215	280mm	2200mm	195 – 277V	Dolne, Góra	Powłoka proszkowa	Stal

Table 3/3

Numer katalogowy	Liczba opakowań
10630-212	1
10630-213	1
10630-214	1
10630-215	1

DODATKOWE INFORMACJE O PRODUKCIE

For trouble-free operation of the air/liquid heat exchanger the quality requirements of the coolant must be maintained; The selection of appropriate anti-corrosion and frost protection agents depends on the environment in which the unit is used and on the external chiller.

At coolant temperatures below 14 °C, there is an increased risk of condensation. We recommend using a condensate management package.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Marki w naszej ofercie:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE